

STRATO-THERM


TE Internal #: 1577616-1

Closed Ring Tongue Terminal, 24 – 22 AWG, M2.5 Stud, 3.02 mm [.119 in] Stud Diameter, Closed Barrel, Straight, Nickel Plating, STRATO-THERM

[View on TE.com >](#)



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: .2 – .4 mm²

Stud Size: M2.5

Stud Diameter: 3.02 mm [.119 in]

Features

Configuration Features

Number of Holes	1
-----------------	---

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Current Rating	1 A
----------------	-----

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Body Features

Product Weight	.55 g[.0193 oz]
Insulation Sleeve Color	Brown
Stripe Color	Brown

Packaging Features

Packaging Quantity	1
Packaging Method	Package



Product Type Features

Shape Description	RING-041
Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	M2.5
Sealable	No
Wire Insulation Support Retention Type	Insulation Support

Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Nickel

Dimensions

Wire Size	.2 – .4 mm <sup>2</sup>
Stud Diameter	3.02 mm[.119 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	18.01 mm[.709 in]
Compatible Insulation Diameter (Max)	1.9 mm[.075 in]
Compatible Insulation Diameter Range	.89 – 1.9 mm[.035 – .075 in]

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1901611-2  
CCII PIDG STRATO 24-20 ASSY

TE Part # 576778  
HHHT PIDG PEEK STRATO 24-22 ASSY

TE Part # 1901611-1  
CCII PIDG STRATO 24-20 ASSY

TE Part # 576711  
SAHT PIDG PEEK STRATO 24-22 DIE SET

Also in the Series | STRATO-THERM











Crimp Wire Pins, Tabs & Ferrules(1)

Ring Terminals(85)

Splices(13)

Customers Also Bought



 <p>TE Part #11029320-00 44036RC, THERM, ROHS</p>	 <p>TE Part #1577619-1 TERMINAL RT PIDG PEEK STRATO 24-22 AWG</p>	 <p>TE Part #1577639-1 TERMINAL RT PIDG PEEK STRATO 14-12 AWG</p>	 <p>TE Part #2-36161-8 TERMINAL, PIDG R IR 10 10</p>
 <p>TE Part #5960064009 TFER-5/8-X-SP</p>	 <p>TE Part #CZ3657-000 SETR08BI-SIDE-ENTRY-TINEL-LOCK-RING</p>	 <p>TE Part #ZPF000000000102759 104-0235-00</p>	 <p>TE Part #ZPF000000000000921 057-0590-80</p>
 <p>TE Part #893803-000 2000P-RIBBON-4TT-MED</p>	 <p>TE Part #ZPF000000000000785 047-0982-03</p>		

Documents

Product Drawings

TERMINAL, PEEK PIDG STRATO, 24-22AWG

English

CAD Files

Customer View Model

ENG\_CVM\_CVM\_1577616-1\_B.2d\_dxf.zip

English

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1577616-1\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1577616-1\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

1577616-1

Closed Ring Tongue Terminal, 24 – 22 AWG, M2.5 Stud, 3.02 mm [.119 in] Stud Diameter, Closed Barrel, Straight, Nickel Plating, STRATO-THERM



Application Specification

English