



Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: 5180 – 13100 CMA

Stud Size: #10

Features

Configuration Features

Number of Holes	1
-----------------	---

Body Features

Product Weight	1.363 g
----------------	---------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece

Product Type Features

Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#10
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support



Contact Features

Barrel Type	Closed
Terminal Orientation	Straight
Terminal Plating Material	Nickel

Dimensions

Wire Size	5180 – 13100 CMA
Stud Diameter	5 mm [.197 in]
Tongue Thickness	.79 mm [.031 in]
Product Length	18.77 mm [.739 in]
Barrel Inside Diameter	3.28 mm [.129 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




REPRESENTATION ONLY

TE Part # 46447  
DAHT STRATO 22-10 ASSY


Customers Also Bought




TE Part #DT06-3S-CE02  
PLG, 3P, BLK, E




TE Part #321884  
TERM, STRAT,SOLIS, HT, 22-16, #4




TE Part #2-520184-4  
ULTRAFAST 250 ASSY REC 22-18  
TPBR LP




TE Part #321898  
DIAMOND GRIP 22-16 HT R 10




TE Part #172339-1  
MINI UMNL PLUG HOUSING 6P




TE Part #2-323680-5  
TERMINAL,SOLIS R HT 12-10 10




TE Part #321892  
DG 22-16COM 22-18MIL HT R 6



TE Part #322332  
DIAMOND GRIP 16-14 HT R 6



TE Part #322337  
DIAMOND GRIP 16-14 HT R 8



TE Part #691091-000  
CWT-9004

Documents

Product Drawings



TERMINAL,SOLIS R HT 12-10 10

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_323680\_V.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_323680\_V.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_323680\_V.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_323680\_J.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_323680\_J.3d\_stp.zip

English

Customer View Model

ENG\_CVM\_323680\_J.2d\_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

STRATO-THERM Terminals & Splices for High Temperature Applications

English

Product Specifications

Application Specification

English