

# CUC-V06-C1PGY-S/R4CE8:1 - RJ45 connector



1414383

<https://www.phoenixcontact.com/us/products/1414383>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 connector, design: RJ45, degree of protection: IP67, number of positions: 8, 1 Gbps, CAT6, material: Plastic, connection method: Crimp connection, connection cross section: AWG 27- 24, cable outlet: straight, color: gray, Ethernet/PROFINET

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 1414383             |
| Packing unit                         | 1 pc                |
| Minimum order quantity               | 1 pc                |
| Sales key                            | AB17                |
| Product key                          | ABNNAB              |
| Catalog page                         | Page 350 (C-2-2019) |
| GTIN                                 | 4055626025346       |
| Weight per piece (including packing) | 19.5 g              |
| Weight per piece (excluding packing) | 19.5 g              |
| Customs tariff number                | 85366990            |
| Country of origin                    | DE                  |

# CUC-V06-C1PGY-S/R4CE8:1 - RJ45 connector



1414383

<https://www.phoenixcontact.com/us/products/1414383>

## Technical data

### Product properties

|                      |                             |
|----------------------|-----------------------------|
| Product type         | Data connector (cable side) |
| Type                 | RJ45                        |
| Sensor type          | Ethernet/PROFINET           |
| Number of positions  | 8                           |
| Connection profile   | RJ45                        |
| No. of cable outlets | 1                           |
| Type                 | RJ45                        |
| Shielded             | no                          |
| Cable outlet         | straight                    |

### Insulation characteristics

|                      |   |
|----------------------|---|
| Overvoltage category | I |
| Degree of pollution  | 2 |

### Electrical properties

|                                         |            |
|-----------------------------------------|------------|
| Rated voltage (III/3)                   | 72 V (DC)  |
| Rated current                           | 1 A        |
| Frequency range                         | to 250 MHz |
| Nominal voltage $U_N$                   | 72 V (DC)  |
| Nominal current $I_N$                   | 1.75 A     |
| Transmission medium                     | Copper     |
| Transmission characteristics (category) | CAT6       |
| Transmission speed                      | 1 Gbps     |

### Connection data

#### Connection technology

|                              |                                                        |
|------------------------------|--------------------------------------------------------|
| Connection method            | Crimp connection                                       |
| Connection cross section AWG | 27 ... 24 (flexible)                                   |
| Conductor cross section      | 0.1 mm <sup>2</sup> ... 0.2 mm <sup>2</sup> (flexible) |

### Dimensions

|        |         |
|--------|---------|
| Width  | 38.4 mm |
| Height | 19.9 mm |
| Length | 53 mm   |

### Material specifications

|                                        |         |
|----------------------------------------|---------|
| Color                                  | gray    |
| Flammability rating according to UL 94 | V0      |
| Seal material cable seal               | TPE     |
| Housing material                       | Plastic |
| Cable seal material                    | NBR     |

# CUC-V06-C1PGY-S/R4CE8:1 - RJ45 connector



1414383

<https://www.phoenixcontact.com/us/products/1414383>

|                          |                 |
|--------------------------|-----------------|
| Contact material         | Phosphor bronze |
| Contact surface material | Gold            |
| Contact carrier material | PC              |
| O-ring material          | FPM             |

## Cable/line

|                         |                     |
|-------------------------|---------------------|
| External cable diameter | 5 mm ... 8.5 mm     |
| Cable cross section     | 0.1 mm <sup>2</sup> |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 750 |
|-----------------------------|-------|

## Environmental and real-life conditions

### Ambient conditions

|                                 |                  |
|---------------------------------|------------------|
| Degree of protection            | IP67             |
| Ambient temperature (operation) | -25 °C ... 60 °C |

# CUC-V06-C1PGY-S/R4CE8:1 - RJ45 connector




1414383

<https://www.phoenixcontact.com/us/products/1414383>

## Drawings

Dimensional drawing



RJ45 sleeve housing IP67

# CUC-V06-C1PGY-S/R4CE8:1 - RJ45 connector



1414383

<https://www.phoenixcontact.com/us/products/1414383>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 27440101 |
| ECLASS-12.0 | 27440113 |
| ECLASS-13.0 | 27440116 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# CUC-V06-C1PGY-S/R4CE8:1 - RJ45 connector



1414383

<https://www.phoenixcontact.com/us/products/1414383>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                                                             |
|-------------------------------------|-------------------------------------------------------------|
| REACH candidate substance (CAS No.) | 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol(CAS: 119-47-1) |
| SCIP                                | 2204a4ca-78a0-44aa-a30d-de720a2b8ca3                        |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)