

2349201-8


✓ ACTIVE

SFP56

TE Internal #: 2349201-8

zSFP+ Stacked (SFP56), Cage Assembly with Integrated Connector,
.6mm [.018in] Centerline, Signal[View on TE.com >](#)

Connectors > Pluggable I/O Connectors & Cages > SFP56 Stacked Cage Assembly: EMI Spring

Form Factor: **zSFP+ Stacked (SFP56)**Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**Centerline (Pitch): **.6 mm [.018 in]**Circuit Application: **Signal**Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**[All SFP56 Stacked Cage Assembly: EMI Spring \(48\)](#)**Features****Termination Features**

Termination Method to PCB

Through Hole - Press-Fit

Operation/Application

Pluggable I/O Applications

SFP28

Circuit Application

Signal

Product Type Features

Cage Type

Stacked

Form Factor

zSFP+ Stacked (SFP56)

Pluggable I/O Product Type

Cage Assembly with Integrated Connector

Configuration Features

Number of Positions

20

Number of Ports

24

Port Matrix Configuration

2 x 12

Electrical Characteristics

Data Rate (Max)	56 Gb/s
-----------------	---------

Housing Features

Centerline (Pitch)	.6 mm [.018 in]
--------------------	-----------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C [-67 – 221 °F]
-----------------------------	-----------------------------

Other

Included Lightpipe	Yes
EMI Containment Feature Type	Internal/External EMI Springs
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 1761394-1
DUST COVER, SFP, GANGED &
STACKED

Also in the Series | **SFP56**



Pluggable I/O Cable Assemblies(17)




Pluggable IO Connectors & Cages(53)

Customers Also Bought



TE Part #6-2213362-2
RCPT ASSY,DIMMABLE
PHOTOCONTROL,150C,3 P



TE Part #1734375-1
CHAMP .050 HIGH RISE, REVERSED



TE Part #2132529-3
IMP100S,H,V3P6C,LG,REW39,5.5



TE Part #5-1375870-4
RCPT ASSY,12 POS,VERT,0.8MM MI



TE Part #2-6450880-4
MBXLE R/A RCPT 4P16S4P



TE Part #1-2170287-1
1X4 CAGE ASSEMBLY, QSFP, SINGLE
SQ LP



TE Part #1734100-3
Champ050 series,30pos,Au over PdNi



TE Part #1734101-3
Champ050 series,30pos,Au over PdNi



Documents

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2349201-8_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2349201-8_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2349201-8_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English