


[Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases](#)Hood & Base Connector Product Type: **Hood**Cable Entry Location: **Bottom**Hood & Base Locking Device Type: **Screwlock**Sealable: **Yes**EU RoHS Compliance: **Compliant**

Features

Operation/Application

Circuit Application

Power & Signal

Mechanical Attachment

Thread Size

M40

Hood & Base Locking Device Type

Screwlock

Product Type Features

Hood & Base Connector Product Type

Hood

Sealable

Yes

Body Features

Cable Entry Location

Bottom

Other

EU RoHS Compliance

Compliant

EU ELV Compliance

Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T3609400102-000
DLX-40-M



TE Part # T2040242101-000
HE-024-M



TE Part # T1930241000-000
H24BPR-AG

Customers Also Bought



TE Part # T2030001015-000
CEM-1.5



TE Part # T1440242125-100
H24B-SGR-M25



TE Part # T2070244001-000
H24BN-T6



TE Part # T1610063125-000
H6B-SGR-M25



TE Part #T2111063101-000
HMN-006-PM



TE Part #T2111063201-000
HMN-006-PF



TE Part #T2030002015-000
CEF-1.5



TE Part #T0931000425-200
CODING-PIN-M3-LSTM



TE Part #T0931006527-200
CODING-PIN-M3-LSTF



TE Part #T1930241000-000
H24BPR-AG

Documents

Product Drawings

H24BPR-TGH-M40

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_T1920241140-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1920241140-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T1920241140-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

HEAVY DUTY CONNECTORS

English

HEAVY DUTY CONNECTORS

Japanese

Product Specifications

Application Specification

English

T1920241140-000

Heavy Duty Connector Hood, Bottom Entry, Screwlock, Sealable



Application Specification