




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **592 – 3260 CMA**

Mating Tab Width: **4.8 mm [.189 in]**

Features

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Connection Capacity	Single
---------------------	--------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Body Features

Insulation Material	Nylon
---------------------	-------

Other

Barrel Color	Red
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Packaging Features

--	--



Packaging Quantity	1000
--------------------	------

Packaging Method	Loose Piece
------------------	-------------

Dimensions

Product Length	20.88 mm[.822 in]
----------------	-------------------

Compatible Insulation Diameter Range	3.56 mm[.14 in]
--------------------------------------	-----------------

Wire Size	592 – 3260 CMA
-----------	----------------

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
--------------------------------	------------

Mating Tab Width	4.8 mm[.189 in]
------------------	-----------------

Mating Tab Thickness	.8 mm[.031 in]
----------------------	----------------

Terminal Orientation	Straight
----------------------	----------

Contact Base Material	Phosphor Bronze
-----------------------	-----------------

Terminal Plating Material	Tin
---------------------------	-----

Crimp Type	Compression Crimp
------------	-------------------

Barrel Type	Closed
-------------	--------

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
--	---

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2392021-1 RED BATTERY DAHT KIT 110V (47689-4)	TE Part # 2323802-9 SSRMP-240D10R = Mini Puck,10A, 240V AC,R	TE Part # 539691-2 ERGO DIE R.B.Y	TE Part # 169404 CERTI-LOK DIE
TE Part # 2323802-2 SSRMP-240D16 = Mini Puck,16A,240V AC	TE Part # 1-2323802-2 SSRMP-480D16R = Mini Puck,16A, 480V AC,R	TE Part # 169400 CERTI-LOK FRAME W/O DIES	TE Part # 2323802-7 SSRMP-240D25R = Mini Puck,25A, 240V AC,R
TE Part # 2323802-6 SSRMP-480D10 = Mini Puck,10A,480V AC	TE Part # 2392021-2 RED BATTERY DAHT KIT 220V (47689-4)	TE Part # 2323802-1 SSRMP-240D25 = Mini Puck,25A,240V AC	TE Part # 2323802-4 SSRMP-480D25 = Mini Puck,25A,480V AC
TE Part # 58423-1 DIE, RBV IS9252	TE Part # 58433-3 PRO CR ASSY, RBV IS9252	TE Part # 47386-4 DAHT PG PIDG 26-16 ASSY	TE Part # 1-2323802-3 SSRMP-480D10R = Mini Puck,10A, 480V AC,R



TE Part # 1-2323802-1
SSRMP-480D25R = Mini Puck,25A,
480V AC,R

TE Part # 525690
DAHT PG PIDG 20-18 ASSY

TE Part # 2323802-8
SSRMP-240D16R = Mini Puck,16A,
240V AC,R

TE Part # 90035-3
DAHT PIDG FASTON 22-18 ASSY

Customers Also Bought

TE Part #926901-3
UNIV-MNL BUCHSE

TE Part #CAT-T3437-ST2999
STD Snap-On Markers

TE Part #F26778-000
ST58-5-00

TE Part #097370-000
TTVF200YW-100

TE Part #2820103008
44A0111-18-0

TE Part #325300
TERMINAL,AMPOWER 1/0 0

TE Part #1-659795-9
FEED FINGER

TE Part #2-1105050-2
HN.D-C-ST1.AU.0,5

Documents

Product Drawings

187 PIDG FASTON REC

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_9-160483-5_J.2d_dxf.zip

English

Customer View Model

ENG_CVM_9-160483-5_J.3d_igs.zip

English

Customer View Model

ENG_CVM_9-160483-5_J.3d_stp.zip

English

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_9-160483-5_L.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-160483-5_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_9-160483-5_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.