




Connectors > Contacts > Connector Contacts



Contact Type: **Pin**
Contact Mating Area Plating Material: **Gold**
Wire Contact Termination Area Plating Material: **Gold**
Contact Retention Within Housing: **With**
Contact Retention Type Within Housing: **Snap-In**

Features

Identification Marking

Contact Color Code	Yellow/Red
--------------------	------------

Packaging Features

Packaging Quantity	900
Packaging Method	Bag

Dimensions

Compatible Insulation Diameter Range	1.02 – 1.57 mm[.04 – .062 in]
Wire Size	.2 – .6 mm²

Mechanical Attachment

Wire Insulation Support	With
Contact Retention Type Within Housing	Snap-In

Contact Features

Contact Underplating Material	Nickel
Contact Orientation	Straight
Mating Pin Diameter	1.57 mm[.062 in]

Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Wire Contact Termination Area Plating Thickness	.76 µm[30 µin]
Contact Mating Area Plating Material Finish	Bright
Contact Type	Pin
Contact Mating Area Plating Material	Gold
Wire Contact Termination Area Plating Material	Gold
Contact Retention Within Housing	With
Contact Size	Size 16
Contact Base Material	Brass
Contact Current Rating (Max)	13 A

Product Type Features

Sealable	No
----------	----

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold:



Pb (2.5% in Component Part)

Article Safe Usage Statements:
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Not applicable for solder process capability
---------------------------	--

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-601967-6 POSITIONER TYPE II CONTACTS	 TE Part # 58541-1 PRO-CRIMPER HAND TOOL & DIE	 TE Part # 213853-1 CPC PLUG ASSEMBLY SIZE 23-19	 TE Part # 206516-1 CPC PLUG ASSEMBLY SIZE 11-4
 TE Part # 211770-2 CPC PLUG ASSEMBLY SIZE 23-19	 TE Part # 796274-2 SLD CPC PLUG ASSY,17-16,STD SX	 TE Part # 200893-2 INSERTION TOOL CONT	 TE Part # 208716-1 CMC PLUG ASSEMBLY,SZ 14



TE Part # 208718-2
CMC PLUG ASSEMBLY, SZ 14-5



TE Part # 213849-1
CPC PLUG ASSEMBLY SIZE 17-16



TE Part # 132312-1
CONTACT PIN TYPE 2 AWG 24-20



TE Part # 796271-1
SLD CPC PLUG ASSY, 17-14, REV SX



TE Part # 796274-1
SLD CPC PLUG ASSY, 17-16, STD SX



TE Part # 1977878-1
SLD CPC PLUG ASY, 11-4, STD SEX, UV RESIST



TE Part # 796188-1
SLD CPC PLUG ASSY, 23-24, STD SX



TE Part # 1977887-1
PLUG ASSY, 23-37 STD SEX THRD AD, UV RESIS



TE Part # 208714-2
CMC PLUG ASSEMBLY, SZ 14-7



TE Part # 211766-1
CPC PLUG ASSEMBLY SIZE 17-9



TE Part # 211772-1
CPC PLUG ASSEMBLY SIZE 23-19



TE Part # 206554-1
CPC PLUG ASSEMBLY SIZE 17-16

Also in the Series | AMP Type II



Connector Contacts(29)



Insertion & Extraction Tools(4)




Power Contacts(29)

Customers Also Bought



TE Part #E17344-000
CM-SCE-TP-1/2-4H-9



TE Part #2-1589455-8
SSL015PC2DC018 = WDUALOBE




TE Part #T2010043201-000
HA-004-FS



TE Part #201570-1
CONTACT PIN ASSY.






TE Part #796274-2
SLD CPC PLUG ASSY,17-16,STD SX




TE Part #YDIV43E17-35PNC009
RECP ASSY



TE Part #218561-000
22759/34-20-0



TE Part #354660-E
STVE 48 F ACE GGG 7-02 1206 4,5 *
247 E



TE Part #1393557-7
C42334A 386C 61=BKLEV 413 BUEG



TE Part #283371-000
44A0111-16-45

Documents

Product Drawings
CONTACT PIN ASSY.

English

CAD Files
Customer View Model
ENG_CVM_201578-1_U.3d_igs.zip

English

Customer View Model
ENG_CVM_201578-1_U.3d_stp.zip

English

Customer View Model
ENG_CVM_201578-1_U.2d_dxf.zip

English

3D PDF

English

3D PDF

3D

Customer View Model
ENG_CVM_CVM_201578-1_AD.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_201578-1_AD.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_201578-1_AD.3d_stp.zip

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMP Circular Connectors for Commercial Signal & Power Applications

English

Signal Contacts

English

M_SERIES_PIN_AND_SOCKET_CONNECTORS

English

Product Specifications

Application Specification

Japanese

Application Specification

English

Type II Screw Machine Contacts

Japanese

Application Specification

Japanese

Instruction Sheets

Instruction Sheet (U.S.)

English

Application and Maintenance for Crimping Die Assemblies

English

Instruction Sheet (U.S.)

Japanese

Instruction Sheet (U.S.)

English

Instruction Sheet (U.S.)

English