



Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Terminating Cover**

Primary Product Color: **Clear**

Primary Product Material: **Polycarbonate**

Operating Temperature (Max): **125 °C [ 257 °F ]**

Operating Temperature Range: **-55 – 125 °C [ -67 – 257 °F ]**

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Product Type Features

Product Profile	Standard
Connector Cover Type	Terminating Cover

Body Features

Primary Product Color	Clear
Primary Product Material	Polycarbonate

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | Z-PACK 2mm HM

Board-to-Board Headers & Receptacles(46)	Connector Contacts(2)	Connector Hardware(91)	Hard Metric Backplane Connectors (267)



High Speed Backplane Connectors(1)



Power Contacts(2)

Customers Also Bought



TE Part #HD36-24-47PE-059  
PLG,47P,AL,E, CBLCLMPBT,DRAIN,16 /20,P,MC



TE Part #WB-60PA  
WEDGE LOCK, 60P, REC, GRY, DRB, A



TE Part #CAT-HST-DWP125  
DWP-125 Heat Shrink Tubing



TE Part #1-967630-4  
FLACHSTE-GEH2,8 21P



TE Part #1-1445022-0  
MICRO MNL RFECEPT HSG SINGLE R



TE Part #66428-3  
III+ SKT,30-26,15AU/FL,LP



TE Part #BSA085F23420235000  
923 PLUG

Documents

Product Drawings

2MM HM DUST PROTECTOR 6U CARD

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_646502-7\_J.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_646502-7\_J.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_646502-7\_J.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Product Specifications

Product Specification

English

Product Specification

English