

Microdot

TE Internal #: 1532216-2

Plug, Cable-to-Board, 100 Position, 1.27 mm [.05 in] Centerline,
Wire & Cable, Signal, Microminiature & Nanominiature D
Connectors[View on TE.com >](#)

Connectors > D-Shaped Connectors > Microminiature & Nanominiature D Connectors

Connector & Housing Type: **Plug**Connector System: **Cable-to-Board**Number of Positions: **100**Centerline (Pitch): **1.27 mm [.05 in]**Connector & Contact Terminates To: **Wire & Cable****Features****Contact Features**Contact Options **Installed**Contact Current Rating (Max) **3 A****Product Type Features**Connector & Housing Type **Plug**Connector System **Cable-to-Board**Connector & Contact Terminates To **Wire & Cable****Configuration Features**Number of Positions **100****Termination Features**Termination Method to Wire & Cable **Solder Cup****Housing Features**Centerline (Pitch) **1.27 mm [.05 in]****Usage Conditions**Operating Temperature Range **-55 – 125 °C [-67 – 257 °F]****Operation/Application**Circuit Application **Signal**

Other

EU RoHS Compliance	Not Compliant
EU ELV Compliance	Not Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Cd (100% in Component Part) <small>Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.</small>
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #CAT-D9934-A75A
DYNAMIC 3100 REC AND TAB HSGTE Part #1827589-2
DYNAMIC D1000 REC CONT 2L AU
0.38um L/PTE Part #1-179958-3
DYNAMIC D-5200S REC HSG 3P K/XTE Part #1-1318120-3
DYNAMIC D-2100 REC HSG 3PTE Part #890103-000
S1124-TAPE-0.75X100-FTTE Part #YDTS20F25-19SNV001
RECP ASSY

Documents

Product Drawings

[M83513/01-HC, MCKS-C2-B-100PS](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_1532216-2_B.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_1532216-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1532216-2_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.