







LSS-130-02-L-DV-A-K

(0.635 mm) .025"

LSS SERIES

SPEED HERMAPHRODITIC STRIP

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?LSS

Insulator Material:

Black Liquid Crystal Polymer Contact Material: Phosphor Bronze Plating: Au or Sn over 50 µ" (1.27 µm) Ni Current Rating: 1.7 A per pin (4 adjacent pins powered)

Operating Temp Range: -55 °C to +125 °C RoHS Compliant:

PROCESSING

Lead-Free Solderable:

Yes SMT Lead Coplanarity: (0.10 mm) .004" max


Board Stacking: For applications requiring two or more connectors per board, contact ipg@samtec.com

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality




APPLICATION





LEAD STYLE	MATED HEIGHT*
-01 & -01	(6.00) .236
-01 & -03	(7.00) .276
-03 & -03	(8.00) .315
-01 & -02	(9.00) .354
-02 & -03	(10.00) .394
-02 & -02	(12.00) .472
*Processing conditions will	

affect mated height

Note: Some lengths, styles and options are non-standard, non-returnable.







LEAD STYLE	Α	В
-01	(4.50) .177	(1.60) .063
-02	(7.49) .295	(4.59) .181
-03	(5.49) .216	(2.59) .102

ALSO AVAILABLE (MOQ Required)

- Locking Clip on -02 or -03 lead style
- Other Gold plating options
- · Other pin counts Contact Samtec.

