

332342

x OBSOLETE


Alcoswitch TPF

TE Internal #: 332342

TE Internal Description: TWIN BNC BHD JACK TEF

[View on TE.com >](#)

Connectors > RF Connectors > Coax Connectors

RF Interface: **Twin BNC**RF Connector Style: **Jack**RF Connector Mated Outer Diameter (Approximate): **10.8 mm [.425 in]**Compatible With RF Cable Type: **RG 108, RG 108A**RF Connector Coupling Mechanism: **Bayonet**

Features

Contact Features

	7620 μ in
RF Connector Center Contact Plating Material	Silver
RF Connector Center Contact Material	Brass

Dimensions

Panel Thickness (Recommended)	3.18 mm [.125 in]
RF Connector Mated Outer Diameter (Approximate)	10.8 mm [.425 in]

Product Type Features

Connector Seal & Plug Type	Gasket
RF Interface	Twin BNC
RF Connector Style	Jack
Compatible With RF Cable Type	RG 108, RG 108A
Connector System	Cable-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Mechanical Attachment

RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Mechanical
Detent	With

Operation/Application

Operating Frequency	4 GHz
---------------------	-------

Configuration Features

Number of Positions	2
Number of Coaxial Contacts	2

Body Features

Cable Connector Orientation	Straight
Body Material	Brass
Body Plating Material	Silver

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Packaging Features

Packaging Method	Carton
------------------	--------

Other

Dielectric Material	PTFE
EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant with Exemptions

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUN 2016 (169) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.







Also in the Series | [Alcoswitch TPF](#)


General Purpose Push Button Switches (13)



Push Button Switches(13)

Customers Also Bought

TE Part #980286-000
242W042-25-0TE Part #293973-000
TXR40AB00-1612AITE Part #806677-000
214A032-25-0TE Part #554173-000
TXR40AB00-1406AITE Part #658819-000
TXR40AB00-1006AITE Part #165805-000
D-602-0144TE Part #430079-000
7528A5314-0TE Part #918455-000
RBD-75-S-00



TE Part #900469-000
RBD-50-M-00

TE Part #4451903001
0024A0311-0

Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_332342_H.2d_dxf.zip](#)
English

Customer View Model
[ENG_CVM_CVM_332342_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_332342_H.3d_stp.zip](#)
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

[Connector, COAXICON, Twin BNC](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English