




Terminals & Splices > PCB Terminals



PCB Terminal Type: **Receptacle**
PCB Hole Diameter: **3.68 mm [.145 in]**
Mating Pin Diameter: **1.47 mm [.058 in]**
Compatible Insulation Diameter (Max): **1.78 mm [.07 in]**
Compatible Insulation Diameter Range: **1.14 – 1.78 mm [.045 – .07 in]**

Features

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Product Type Features

Terminal Features	Stud Hole
Wire Insulation Support Retention Type	Open Barrel

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Dimensions

Terminal Material Thickness	.25 mm[.01 in]
PCB Hole Diameter	3.68 mm[.145 in]
Compatible Insulation Diameter (Max)	1.78 mm[.07 in]
Compatible Insulation Diameter Range	1.14 – 1.78 mm[.045 – .07 in]
Wire Size	.2 – .6 mm²



Contact Features

Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
PCB Terminal Type	Receptacle
Mating Pin Diameter	1.47 mm[.058 in]
Terminal Plating Material	Gold
Contact Underplating Material	Nickel
Terminal Orientation	Straight

Termination Features

Termination Method to PCB	Through Hole - Solder
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 91507-1
CCII .058 REC P.C. 24-20 ASSY



TE Part # 60986-1
.058 DIA PIN RECPT L/P




TE Part # 60940-1
.058 PIN REC 24-20 010PTPPHBZ

Customers Also Bought




TE Part #8-215570-2
MICRO-MATCH PBC.12P




TE Part #281739-5
HEADER HE14 STRAIGHT 2X5 P



TE Part #1-338068-2
MICRO-MATCH FTE,12P




TE Part #1-2273011-1
M8 x 1.0 Angled socket Pigtail




TE Part #3-60803-1
.058 DIA PIN PC AUSN/NI/PHBZ LF




TE Part #2205072-3
CA MICRO-MATCH MOW-PB 12POS




TE Part #374380-E
STVE 160 FI ABCDE VVVV 7-03 TL-S
** 2



TE Part #384298-E
STVE 160 M ABCDE VVVV 4-00 0606
** 137



TE Part #384299-E
STVE 160 M ABCDE VVVV 4-00 0606
** 247



TE Part #8-1579002-0
SUPER CHAMP III

Documents



CAD Files

3D PDF

English

Customer View Model

ENG_CVM_60789-3_AE.3d_igs.zip

English

Customer View Model

ENG_CVM_60789-3_AE.3d_stp.zip

English

Customer View Model

ENG_CVM_60789-3_AE.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_60789-3_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_60789-3_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_60789-3_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS

English

Product Specifications

Application Specification

English