

SACC-M12MS-5CON-PG 9-M - Connector



1681460

<https://www.phoenixcontact.com/us/products/1681460>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 5-position, Plug straight M12, coding: A, Screw connection, knurl material: Zinc die-cast, nickel-plated, cable gland Pg9, external cable diameter 6 mm ... 8 mm

Your advantages

- Safe use in the field, thanks to a high degree of protection
- Screw connection: proven connection technology for a large selection of different conductors

Commercial data

| | |
|--------------------------------------|--------------------|
| Item number | 1681460 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF30 |
| Product key | BF2CAA |
| Catalog page | Page 22 (C-2-2019) |
| GTIN | 4017918157432 |
| Weight per piece (including packing) | 24.17 g |
| Weight per piece (excluding packing) | 24.2 g |
| Customs tariff number | 85366990 |
| Country of origin | HU |

SACC-M12MS-5CON-PG 9-M - Connector



1681460

<https://www.phoenixcontact.com/us/products/1681460>

Technical data

Notes

Assembly note

NOTE: Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.

Product properties


| | |
|----------------------|---------------------------------|
| Product type | Circular connector (cable-side) |
| Sensor type | Universal |
| Number of positions | 5 |
| No. of cable outlets | 1 |
| Shielded | no |
| Coding | A |
| Cable outlet | straight |
| Pg screw connection | Pg9 |

Insulation characteristics

| | |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution | 3 |

Dimensions

Dimensional drawing



| | |
|--------|-------|
| Width | 20 mm |
| Height | 20 mm |
| Length | 60 mm |

External dimensions

| | |
|------------------|---------------|
| Outside diameter | 6 mm ... 8 mm |
|------------------|---------------|

Housing

| | |
|------------------|-------|
| Diameter housing | 20 mm |
|------------------|-------|

Material specifications

| | |
|--|--------|
| Flammability rating according to UL 94 | HB |
| Seal material | NBR |
| Material of grip body | PA |
| Contact material | CuZn |
| Contact surface material | CuSnZn |
| Contact carrier material | PA |

SACC-M12MS-5CON-PG 9-M - Connector



1681460

<https://www.phoenixcontact.com/us/products/1681460>

| | |
|-------------------------------|------------------------------|
| Material for screw connection | Zinc die-cast, nickel-plated |
|-------------------------------|------------------------------|

Connection data

Conductor connection

| | |
|---|---|
| Connection method | Screw connection |
| Connection cross section | 0.25 mm ² ... 0.75 mm ² (without ferrule) |
| | 0.14 mm ² ... 0.75 mm ² (with ferrule) |
| | 0.25 mm ² ... 0.75 mm ² (solid) |
| Connection cross section AWG | 24 ... 18 (without ferrule) |
| | 26 ... 20 (with ferrule) |
| Stripping length of the individual wire | 5 mm |
| Tightening torque | 0.4 Nm (M12 knurl) |
| | 0.2 Nm (Screw terminal blocks) |
| | 0.8 Nm ... 1 Nm (Pressure screw with sleeve housing) |

Electrical properties

| | |
|--------------------------------|----------|
| Rated surge voltage | 1.5 kV |
| Contact resistance | ≤ 8 mΩ |
| Insulation resistance | ≥ 100 MΩ |
| Nominal voltage U _N | 48 V AC |
| | 60 V DC |
| Nominal current I _N | 4 A |

Mechanical properties

Mechanical data

| | |
|-----------------------------|------|
| Insertion/withdrawal cycles | ≥ 50 |
|-----------------------------|------|

Connector

Connection 1

| | |
|-------------------|----------|
| Head design | Plug |
| Head cable outlet | straight |
| Head thread type | M12 |
| Coding | A |

Cable/line

| | |
|---|-----------|
| Signal type/category | Universal |
| Stripping length of the individual wire | 5 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|----------------------------------|
| Degree of protection | IP67 |
| Ambient temperature (operation) | -40 °C ... 85 °C (Plug / socket) |

SACC-M12MS-5CON-PG 9-M - Connector



1681460

<https://www.phoenixcontact.com/us/products/1681460>

Standards and regulations

| | |
|--------------------------|-----------------|
| Standard designation | M12 connector |
| Standards/specifications | IEC 61076-2-101 |

SACC-M12MS-5CON-PG 9-M - Connector


1681460

<https://www.phoenixcontact.com/us/products/1681460>



Drawings

Schematic diagram




Pin assignment M12 male connector, 5-pos., A-coded, male side

SACC-M12MS-5CON-PG 9-M - Connector


1681460

<https://www.phoenixcontact.com/us/products/1681460>



Male/Female M12

Dimensional drawing



Plug, M12 x 1, straight


SACC-M12MS-5CON-PG 9-M - Connector

1681460

<https://www.phoenixcontact.com/us/products/1681460>



Schematic diagram



Cable connection side M12 (screw connection)

SACC-M12MS-5CON-PG 9-M - Connector





1681460

<https://www.phoenixcontact.com/us/products/1681460>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1681460>

| | | | | |
|---|--------------------------------|--------------------------------|-------------------|-------------------------------|
|  cUL Recognized Approval ID: FILE E 221474 | | | | |
| | Nominal voltage U _N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| | 60 V | 4 A | - | - |

| | | | | |
|--|--------------------------------|--------------------------------|-------------------|-------------------------------|
|  UL Recognized Approval ID: FILE E 221474 | | | | |
| | Nominal voltage U _N | Nominal current I _N | Cross section AWG | Cross section mm ² |
| | 60 V | 4 A | - | - |

| | | | | |
|-------------------------|--|--|--|--|
| cULus Recognized | | | | |
|-------------------------|--|--|--|--|

SACC-M12MS-5CON-PG 9-M - Connector



1681460

<https://www.phoenixcontact.com/us/products/1681460>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27440102 |
| ECLASS-12.0 | 27440116 |
| ECLASS-13.0 | 27440116 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SACC-M12MS-5CON-PG 9-M - Connector



1681460

<https://www.phoenixcontact.com/us/products/1681460>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 8e48a8c2-9972-4185-b24e-cf055e36b198 |

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com