

2-324469-2

✓ ACTIVE

AMPOWER

TE Internal #: 2-324469-2

Butt Splice, 800 kcmil, 750000 – 850000 CMA, Copper, Gray, Length 84.07 mm [3.31 in], Box, Closed Barrel, Stranded Wire, Copper Wire, Discrete Wire

[View on TE.com >](#)

Terminals & Splices > Splices > AMPOWER Butt Splice



Splice Type: **Butt Splice**

Sealable: **No**

Barrel Inside Diameter: **31.8 mm [1.252 in]**

Wire Size: **800 kcmil**

[All AMPOWER Butt Splice \(18\)](#)

Features

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Industry Standards

Compatible With Agency/Standards Products	UL
Compatible With Approved Standards Products	UL E13288

Configuration Features

Splice Configuration	Single to Single
Compatible With Wire & Cable Type	Discrete Wire

Packaging Features

Packaging Quantity	25
Packaging Method	Box

Contact Features

	150 μ in
Terminal Plating Material	Tin
Contact Base Material	Copper
Barrel Type	Closed

Dimensions

	1.518 in
Barrel Inside Diameter	31.8 mm[1.252 in]
Wire Size	800 kcmil
Product Length	84.07 mm[3.31 in]

Product Type Features

Splice Accessory Type	Splice
Splice Type	Butt Splice
Sealable	No
Compatible With Discrete Wire Type	Stranded

Body Features

Primary Product Color	Gray
Mechanical Attachment	
Wire Insulation Support	Without

Usage Conditions

Insulation Option	Uninsulated
Operation/Application	
Compatible With Wire Base Material	Copper

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 46758-2
[HYP8 AMPOWER 800MCM DIE SET](#)

Customers Also Bought



TE Part #CAT-AM74-AM74L
[AMPOWER Parallel Splice](#)



TE Part #36809
[TERMINAL,SOLIS R 6 5/8](#)



TE Part #2-324466-2
[SPLICE,AMPOWER BUTT 500MCM](#)



TE Part #2-1393104-7
[KRPA-11AG-240-KRPA](#)

Documents

Product Drawings

[SPLICE,AMPOWER BUTT 800MCM](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2-324469-2_AA.2d_dxf.zip](#)

English

Customer View Model[ENG_CVM_CVM_2-324469-2_AA.3d_igs.zip](#)

English

Customer View Model[ENG_CVM_CVM_2-324469-2_AA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.**Datasheets & Catalog Pages**[AMPOWER Terminals and Splices Flyer](#)

English

Instruction Sheets[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals[UL Report](#)

English