



IMPACT

TE Internal #: 2057405-1
60 Position High Speed Backplane Connector, 6 Row, 10 Column,
PCB Mount Receptacle, Right Angle, Unshrouded, 1.9 mm [.075 in]
Centerline, IMPACT

[View on TE.com >](#)

Connectors > PCB Connectors > Backplane Connectors > High Speed Backplane Connectors



Number of Positions: 60
Row-to-Row Spacing: 1.35 mm [.053 in]
Mating Alignment: With
Mating Alignment Type: Polarization
Number of Rows: 6

Features

Electrical Characteristics

Operating Voltage	30 VDC
Impedance	100 Ω

Signal Characteristics

Data Rate	20 – 25 Gb/s
Number of Differential Pairs per Column	2

Industry Standards

UL Flammability Rating	UL 94V-0
Compatible With Approved Standards Products	UL E28476

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	1.2 mm[.047 in]

Body Features

Primary Product Color	Black
-----------------------	-------

Packaging Features

Packaging Method	Tube, Box & Tube
------------------	------------------

Contact Features

Contact Underplating Material	Nickel
-------------------------------	--------



Contact Underplating Material Thickness	1.27 µm[50 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	.762 µm[30 µin]
PCB Contact Termination Area Plating Material Thickness	1.27 µm[50 µin]
Contact Shape & Form	Dual Beam
Contact Layout	Inline
Contact Mating Area Plating Material	Gold
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Type	Socket
Contact Current Rating (Max)	.75 A

Housing Features

Number of Shrouded Sides	0
End Wall Location	None
Housing Material	LCP - GF (Liquid Crystal Polymer)
Centerline (Pitch)	1.9 mm[.075 in]

Product Type Features

Signal Arrangement	Differential
Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
PCB Connector Assembly Type	PCB Mount Receptacle
Shroud Style	Unshrouded

Mechanical Attachment

Guide Hardware	Without
PCB Mount Retention	With
Mating Retention	Without
PCB Mount Retention Type	Action/Compliant Tail
Mating Alignment	With
Mating Alignment Type	Polarization
Connector Mounting Type	Board Mount

Dimensions

PCB Thickness (Recommended)	1.6 mm
Connector Width	20.1 mm[.791 in]



PCB Hole Diameter	.39 mm[.015 in]
Connector Height	10.9 mm[.429 in]
Connector Length	19 mm[.748 in]
Row-to-Row Spacing	1.35 mm[.053 in]

Configuration Features

Number of Pairs	20
Number of Ground Positions	20
Number of Signal Positions	40
Stackable	No
Number of Positions	60
Number of Rows	6
Number of Columns	10
PCB Mount Orientation	Right Angle
Guide Location	Unguided

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC



Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2143016-3 IMP100S,H,RA2P10C,LG,OEW39,5.5	 TE Part # 2143012-2 IMP100S,H,RA2P10C,UG,OEW39,4.9	 TE Part # 2143015-2 IMP100S,H,RA2P10C,UG,REW39,4.9	 TE Part # 2057418-2 IMP100S,H,V2P10C,LG,OEW46,4.9
 TE Part # 2143017-3 IMP100S,H,RA2P10C,LG,REW39,5.5	 TE Part # 2143012-3 IMP100S,H,RA2P10C,UG,OEW39,5.5	 TE Part # 2057431-1 IMP100S,H,V2P10C,UG,LEW39,4.5	 TE Part # 2057423-3 IMP100S,H,V2P10C,RG,OEW39,5.5
 TE Part # 2057427-3 IMP100S,H,V2P10C,UG,LEW46,5.5	 TE Part # 2057419-3 IMP100S,H,V2P10C,LG,OEW39,5.5	 TE Part # 2057432-1 IMP100S,H,V2P10C,UG,DEW39,4.5	 TE Part # 2057424-3 IMP100S,H,V2P10C,RG,LEW46,5.5



TE Part # 2057430-2
IMP100S,H,V2P10C,UG,OEW39,4.9



TE Part # 2057418-3
IMP100S,H,V2P10C,LG,OEW46,5.5



TE Part # 2057424-1
IMP100S,H,V2P10C,RG,LEW46,4.5



TE Part # 2057433-1
IMP100S,H,V2P10C,UG,REW39,4.5



TE Part # 2143015-3
IMP100S,H,RA2P10C,UG,REW39,5.5



TE Part # 2057428-3
IMP100S,H,V2P10C,UG,DEW46,5.5




TE Part # 2057429-3
IMP100S,H,V2P10C,UG,REW46,5.5



TE Part # 2057430-1
IMP100S,H,V2P10C,UG,OEW39,4.5

Also in the Series | IMPACT



High Speed Backplane Connectors
(149)

Customers Also Bought



TE Part #1-1600960-8
CONT 8-10 AWG PWR, STD PLATE &



TE Part #2143012-3
IMP100S,H,RA2P10C,UG,OEW39,5.5



TE Part #2007820-2
IMP100S,H,V4P10C,UG,OEW39,4.9



TE Part #2057416-1
IMP100S,R,RA4P8C,RG,39



TE Part #5-1971846-2
2P, RAST 5 Tab Header, THV





TE Part #1-2271451-4
14 PIN BTB CONNECTOR, PIN HDR ASSEMBLY



TE Part #2057439-2
IMP100S,H,V4P8C,RG,OEW39,4.9



TE Part #4-1971846-2
2P, RAST 5 Tab Header, THV



Documents

Product Drawings

IMP100S,R,RA2P10C,UG,39

English

CAD Files

Customer View Model

ENG_CVM_CVM_2057405-1_A.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2057405-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2057405-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

7-1773458-1_IMPACT_BACKPLANE_CONNECTOR_SYSTEM_CATALOG

English

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English