

RLC73N2AR11FTDF

✓ ACTIVE

CGS | CGS RLC73

TE Internal #: 2-2176571-2

Surface Mount Current Sensing Resistor, Thick Film, 0805, .125 W, .11 ohm, 1 %, ±300 ppm/°C, Solder, 2 Terminations, CGS RLC73

[View on TE.com >](#)



Passive Components > Resistors > Surface Mount Resistors



Resistor Type: **Current Sensing Resistor**
Element Type: **Thick Film**
Package Size Code: **0805**
Power Rating: **.125 W**
Resistance Value: **.11 Ω**

Features

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±300 ppm/°C

Product Type Features

Resistor Type	Current Sensing Resistor
Element Type	Thick Film
Package Size Code	0805

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Power Rating	.125 W
Resistance Value	.11 Ω
Resistance Class	Up to 1kΩ
Passive Component Tolerance	1 %

Termination Features



Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Dimensions

Product Height	.55 mm[.022 in]
Product Length	2 mm[.079 in]
Product Width	1.25 mm[.049 in]

Packaging Features

Packaging Method	Taped & Reeled
------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling

RLC73N2AR11FTDF

Surface Mount Current Sensing Resistor, Thick Film, 0805, .125 W, .11 ohm, 1 %, ±300 ppm/°C, Solder, 2 Terminations, CGS RLC73



based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

TE Part # 2-2176569-2

RLC73N 2A R11 1% 5K RL

Also in the Series | CGS RLC73

Surface Mount Resistors(2392)

Customers Also Bought

TE Part #0413-217-1605

SEALING PLUG, SIZE 16, LOCKING, WHT

TE Part #2176156-7

TLM 1206 0.5W R033 5% 100PPM 5K RL

TE Part #4-2176456-0

CPF 0603 2R55 0.1% 25ppm 1K RL

TE Part #6-2176571-8

RLC73K 2A R332 1% 1K RL

TE Part #2-2176571-7

RLC73N 2A R124 1% 1K RL

TE Part #2-2176571-9

RLC73N 2A R13 1% 1K RL

TE Part #3-2176571-5

RLC73N 2A R15 1% 1K RL

TE Part #2-2176584-2

RLC73PD 2B 1R0 1% 1K RL

RLC73N2AR11FTDF

Surface Mount Current Sensing Resistor, Thick Film, 0805, .125 W, .11 ohm, 1 %, ±300 ppm/°C, Solder, 2 Terminations, CGS RLC73



Documents

Product Drawings

RLC73N 2A R11 1% 1K RL

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-2176571-2_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-2176571-2_BA.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2-2176571-2_BA.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SMD Low Ohmic - Current Sense Resistors - Type RLC73 Series

English