



All High Pin Count Header (52)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)





EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer






This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 963872-2 FLACHSTECKER 1,6MM	 TE Part # 3-929991-1 MESSER 3,0	 TE Part # 1-962526-1 MESSERLEI-GH MIX70P	 TE Part # 963361-1 SEALING F/70P HSG
 TE Part # 1-968879-1 MT2/JPT70P BUGH KPL	 TE Part # 3-929991-2 MESSER 3,0		

Also in the Series | Timer Connector System

 Automotive Connector Caps & Covers (13)	 Automotive Connector Locks & Position Assurance(15)	 Automotive Headers(40)	 Automotive Housings(207)
 Connector Seals & Cavity Plugs(36)	 Crimp Terminal Housings(13)	 Insertion & Extraction Tools(18)	 Other Automotive Connector Accessories(1)
 PCB Headers & Receptacles(40)	 Wire-to-Board Headers & Receptacles (39)		




Customers Also Bought




TE Part #1-207121-0
METRIMATE PIN HDR ASY,36P LF




TE Part #7-1676481-3
CPF 0603 6K8 0.1% 25PPM 1K RL



TE Part #2-2176308-7
RP 1E 0.1W 249K 0.1% 25PPM 5K RL




TE Part #776228-4
23POS,PIN DIA 1.3,HDR ASSY,
180DEG,COD 4



TE Part #1-776163-6
35POS,PIN DIA 1.3,HDR ASSY,90DEG,
COD 6



TE Part #9-1879160-5
RN 0805 9R76 0.1% 10PPM 1K RL



TE Part #4-1625865-0
RP 2A 6R19 0.1% 15PPM CUT LENGTH



TE Part #3-968976-9
MCP2.8 BU-GEH 3P



TE Part #185740-1
12pos MQS .63 header 90deg



TE Part #188685-2
STD TIMER PCB CONTACT

Documents

Product Drawings

MESSERLEISTE MIX70P

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-963484-1_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-963484-1_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-963484-1_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Product Specifications

70 pos. - Coupling for Junior-Power-Timer Contact & Micro - Timer Contact

English

Product Specification

English