



Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.82 – 2.08 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Locking Lance

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece/Carton

Dimensions

Product Length	20.32 mm[.8 in]
Compatible Insulation Diameter Range	3.1 – 4.1 mm[.12 – .16 in]
Terminal Material Thickness	.41 mm[.016 in]



Wire Size	.82 – 2.08 mm²
-----------	----------------

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 90165-1
DAHT 250 FASTON REC 18-14 ASSY



TE Part # 42924-2
FF 250 REC 18-14AWG TPBR PRE CRIMPED



TE Part # 58524-2
PROCRIMPER DIE



TE Part # 58524-1
PROCRIMPER TOOL & DIE



TE Part # 1-1579007-4
EXTRACTION TOOL




TE Part # 4-1579007-3
EXTRACTION TOOL KIT

Also in the Series | FASTIN-FASTON 250




Crimp Terminal Housings(207)



Insertion & Extraction Tools(2)



PCB Terminals(2)



Quick Disconnects(250)

Customers Also Bought



TE Part #205209-2
RECP ASSY SIZE 4



TE Part #5-6609107-3
PS0SXDSPA=C1110



TE Part #554954-1
PLUG KIT,50 POSN, SCR LK, SHLD



TE Part #5749202-2
50 50SR KIT,75D,UK



TE Part #182916-1
CPC SQ.FL.RCPT STD SEX




TE Part #1-968720-1
32pos MQS .63 header 90deg




TE Part #350851-7
UMNL SOK 24-18 AUNIBR



TE Part #1614891-5
CPF 0805 69R8 0.1% 25PPM 1K RL



TE Part #326800
TERMINAL,AMPOWER 1/0 3/8



TE Part #827050-1
25 POS TAB HSG

Documents

Product Drawings

FF 250 REC 18-14AWG TPBR LP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_42282-2_AL_c-42282-2-al.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_42282-2_AL_c-42282-2-al.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_42282-2_AL_c-42282-2-al.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



FASTIN_FASTON_Product_Line

English

Product Specifications

Application Specification

English