

120943-6 ✓ ACTIVE

Z-PACK 2mm HM

TE Internal #: 120943-6

PCB Mount Receptacle, Right Angle, Board-to-Board, 8 Position, 3 mm [.118 in] Centerline, Fully Shrouded, Gold, Z-PACK 2mm HM

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Right Angle**

Connector System: **Board-to-Board**

Number of Positions: **8**

Number of Rows: **1**

## Features

### Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

### Dimensions

Connector Width	25 mm [.984 in]
Connector Height	9.95 mm [.392 in]
Connector Length	24.5 mm [.964 in]

### Packaging Features

Packaging Quantity	19
Packaging Method	Tube

### Industry Standards

Compatible With Approved Standards Products	UL E28476
Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

### Usage Conditions

Operating Temperature (Max)	125 °C [257 °F]
Operating Temperature Range	-55 – 125 °C [-67 – 257 °F]

### Mechanical Attachment

Panel Mount Feature	Without
Mating Retention	Without

PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	Without

#### Termination Features

Termination Post & Tail Length	2 mm[.079 in]
Termination Method to PCB	Through Hole - Press-Fit

#### Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 $\mu\text{m}$ [50 $\mu\text{in}$ ]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	.76 $\mu\text{m}$ [30 $\mu\text{in}$ ]
PCB Contact Termination Area Plating Material Thickness	.5 – 1.25 $\mu\text{m}$ [19.68 – 49.21 $\mu\text{in}$ ]
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold
Contact Type	Receptacle
Contact Current Rating (Max)	16 A

#### Housing Features

Mating Entry Location	Side
Housing Material	Polyester
Centerline (Pitch)	3 mm[.118 in]

#### Configuration Features

Number of Loaded Positions	8
Number of Power Positions	8
Connector Contact Load Condition	Fully Loaded
PCB Mount Orientation	Right Angle
Number of Positions	8
Number of Rows	1

#### Product Type Features

Mixed & Hybrid Header	No
Connector Shape	Rectangular

PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

### Body Features

Primary Product Color	Gray
-----------------------	------

### Operation/Application

Circuit Application	Power
---------------------	-------

### Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability





#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | Z-PACK 2mm HM



## Customers Also Bought



TE Part #1367147-1  
SFP COVER, UNPLATEDTE Part #1551920-2  
zQSFP+ connector assemblyTE Part #1658621-9  
40 NOVO MIL/CTR 15DP,LEAD FREETE Part #203346-E  
MJIM IMV 1X1 S 810 \* X R THRU \* L9A  
M5B0TE Part #214787-E  
EPSVA KS GDM4 EE 6 3,8 SN \*  
STROMVERSORGTE Part #354410-E  
STVR 96 MI ABC VVV 4-00 EE 6,0 8292  
247

## Documents

### Product Drawings

#### ASSEMBLY, R/A UPM RECPT, 8 POS

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_120943-6\\_A.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_120943-6\\_A.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_120943-6\\_A.3d\\_stp.zip](#)

English

### Datasheets & Catalog Pages

#### POWER\_CONNECTORS\_CATALOG\_SEC01\_BOARD\_TO\_BOARD

English

#### Solutions for AdvancedTCA, AdvancedTCA 300, MicroTCA, and AdvancedMC Standards Datasheet 3-1773445-8

English

#### 2\_PIECE\_POWER\_CONNECTORS\_qrg\_4-1773458-1

English

### Product Specifications

## Engineering Report

English