


Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **General Purpose Signal Relay**

Current Type: **DC**

Coil Magnetic System: **Non-Polarized, Monostable**

Contact Arrangement: **2 Form C DPDT-CO**

Contact Current Rating: **1 A**

## Features

### Usage Conditions

Operating Temperature Range	-65 – 125 °C
Environmental Ambient Temperature (Max)	125 °C[257 °F]

### Electrical Characteristics

Coil Resistance	100 Ω
Contact Switching Voltage (Max)	28 VDC
Contact Current Rating	1 A
Coil Voltage Rating	5 VDC
Coil Power Rating DC	.25 W

### Configuration Features

Coil Special Features	Coil Suppression Diode, Coil Polarity Protection Diode
Pin Configuration	.175" Diameter Mounting Pad
Relay Options	MOSFET Driver
Contact Arrangement	2 Form C DPDT-CO

### Operation/Application

Vibration Resistance	30G's, 10 – 3000Hz
Shock Resistance	75G's, 6ms
Current Type	DC

Coil Magnetic System

Non-Polarized, Monostable

**Product Type Features**

Relay &amp; Contactor Type

General Purpose Signal Relay

**Body Features**

Enclosure Type

Hermetically Sealed

**Termination Features**

Main Termination &amp; Connection Type

Extended Leads

Coil Termination &amp; Connection Type

Extended Leads

**Mechanical Attachment**

Product Mount Type

Board Mount

**Other**

EU RoHS Compliance

Not Compliant

EU ELV Compliance

Not Compliant

**Product Compliance**For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU

Not Compliant

EU ELV Directive 2000/53/EC

Not Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2024  
(241)Candidate List Declared Against: JAN 2022  
(223)

Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per  
homogenous material. Also BFR/CFR/PVC  
Free

Solder Process Capability

Not lead free process capable

## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides

on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



TE Part # 2-1617030-7  
HFW1201G01M = M39016/6-116M


## Customers Also Bought



TE Part #5750678-1  
09 RCPT SP/FMS (RET SL)



TE Part #5061850001  
TMS-SCE-1/2-2.0-9



TE Part #5745174-1  
CABLE CLAMP KIT,SZ 4



TE Part #5-2316113-6  
2MM,REC,CNT,CRIMP,24-28AWG,0.76  
UM,LP



TE Part #YDTS26W15-35SNV001  
PLUG ASSY



TE Part #YDTS26W13-98SNV001  
PLUG ASSY



TE Part #NB13034001  
RNF-100-1-BK-FSP



TE Part #1-102387-2  
64 MODIV HSG COMP DR .100 POL



TE Part #443975-5  
AMPLIMITE,RCPT ASY,POSTD,109,5



TE Part #1532176-3  
M83513/04-F03N, MCKS-N1-B-  
37S6G9-18.0

## Documents

### CAD Files

[3D PDF](#)

[3D](#)

**Customer View Model**

[ENG\\_CVM\\_CVM\\_5-1617350-7\\_A.2d\\_dxf.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_5-1617350-7\\_A.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_5-1617350-7\\_A.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Datasheets & Catalog Pages**

[5-1773450-5\\_sec1\\_MGST](#)

English