

HDP26-18-8SE-L017

✓ ACTIVE

DEUTSCH | DEUTSCH HDP, DEUTSCH HD

TE Internal #: HDP26-18-8SE-L017

8 Position Housing, Housing for Female Terminals, Wire-to-Panel, Sealable, Black, Wire & Cable, Power, Panel Mount, Hybrid

[View on TE.com >](#)



Connectors > Automotive Connectors > Automotive Housings > DEUTSCH HDP20 Housings



Number of Positions: 8

Connector & Housing Type: **Housing for Female Terminals**

Mating Pin Diameter: 2.4 mm [.094 in]

Connector System: **Wire-to-Panel**

Sealable: **Yes**

[All DEUTSCH HDP20 Housings \(357\)](#)

Features

Housing Features

Housing Material	PA 66 GF
------------------	----------

Industry Standards

IP Rating	IP67
UL Flammability Rating	UL 94V-0

Dimensions

Compatible Insulation Diameter Range	3.6 – 5.2 mm[.14 – .204 in]
Product Width	43.2 mm[1.7 in]
Product Length	43.2 mm[1.7 in]
Connector Height	41.5 mm[1.63 in]

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Mechanical Attachment

Strain Relief	Without
Terminal Position Assurance	No
Mating Alignment Type	Polarizing Slot



Mating Alignment	With
Connector Mounting Type	Panel Mount

Other

Serviceable	Yes
Connector Position Assurance Capable	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Electrical Characteristics

Operating Voltage	250 VDC
Nominal Voltage Architecture	250 V

Body Features

Cable Exit Angle	180°
Primary Product Color	Black

Contact Features

Contact Size	Size 12
Contact Type	Socket
Mating Pin Diameter	2.4 mm[.094 in]
Contact Current Rating (Max)	25 A

Product Type Features

Mixed & Hybrid Connector	No
Connector Shape	Circular
Connector & Housing Type	Housing for Female Terminals
Connector System	Wire-to-Panel
Sealable	Yes
Primary Locking Feature	Contact Retainer
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Blank Cavity Position	0
Connector Modification	Ring Adapter
Connector Seal Code	E Seal
Number of Positions	8

Usage Conditions



Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1062-12-0144
SOC, SF, SIZE 12, 12-14, AU/SN

TE Part # 1062-12-0222
SOC, SF, SIZE 12, 10, NI/NI

TE Part # HD30-18BT-BK
BOOT, 18SZ, ST, BLK

TE Part # 1062-12-0244
SOC, SF, SIZE 12, 10, AU/SN



TE Part # 1062-12-0166
SOC, SF, SIZE 12, 12-14, NI/SN



TE Part # 0411-337-1205
EXT TOOL, SIZE 12, 12-14 AWG, E, ORG



TE Part # CAT-H396-B128
DEUTSCH HDP20 Backshells



TE Part # CAT-D48-SP729
DEUTSCH Sealing Plugs



TE Part # CAT-H396-CH8172
DEUTSCH HDP20 Housings



TE Part # HD30-18BT-90-BK
BOOT, 18SZ, RA, BLK



TE Part # CAT-D48-ST273
DEUTSCH Solid Contacts

Also in the Series | **DEUTSCH HD**



Automotive Connector Caps & Covers
(4)



Automotive Housings(357)



Connector Strain Relief(5)



Other Automotive Connector
Accessories(6)

Also in the Series | **DEUTSCH HDP**



Automotive Connector Caps & Covers
(4)



Automotive Housings(357)



Insertion & Extraction Tools(11)



Other Automotive Connector
Accessories(6)

Customers Also Bought

HDP26-18-8SE-L017

8 Position Housing, Housing for Female Terminals, Wire-to-Panel, Sealable, Black, Wire & Cable, Power, Panel Mount, Hybrid



TE Part #2292799-3
AS16, PLUG BACKSHELL KIT, ST, 04P, NC12



TE Part #DT04-2P-EE01
REC, 2P, BLK, N, XCAP




TE Part #CAT-H396-CH8172
DEUTSCH HDP20 Housings



TE Part #1062-12-0222
SOC, SF, SIZE 12, 10, NI/NI



TE Part #1060-12-0222
PIN, SF, SIZE 12, 10, NI/NI



TE Part #170327-1
250 PL MKII REC. 22-18AWG PTBR



TE Part #1-1414469-0
V23134J0052X461-EV-CBOX



TE Part #4-967626-1
TAB HSG 2.8MM 9POS.

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_HDP26-18-8SE-L017_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_HDP26-18-8SE-L017_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_HDP26-18-8SE-L017_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

DEUTSCH HD30 & HDP20 CONNECTOR SERIES

English

ICT Terminals and Connectors Catalogue

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

Agency Approvals



[UL Report](#)

English