

2314979-1  ACTIVE

TE Internal #: 2314979-1

CFP2, Cage Assembly, Sealable, Operating Temperature Range -55 – 85 °C [-67 – 185 °F], 1 Ports, Port Matrix Configuration 1 x 1, Included Lightpipe

[View on TE.com >](#)



Connectors > Pluggable I/O Connectors & Cages



Form Factor: **CFP2**

Pluggable I/O Product Type: **Cage Assembly**

Sealable: **Yes**

Operating Temperature Range: **-55 – 85 °C [-67 – 185 °F]**

Number of Ports: **1**

Features

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
---------------------------	--------------------------

Dimensions

Product Width	45.2 mm
---------------	---------

Product Length	78 mm
----------------	-------

PCB Thickness (Recommended)	3 mm [.118 in]
-----------------------------	----------------

Operation/Application

Heat Sink Compatible	Yes
----------------------	-----

Mechanical Attachment

PCB Mounting Style	Double-Sided (Belly-to-Belly)
--------------------	-------------------------------

Body Features

Heat Sink Style	Fin
-----------------	-----

Heat Sink Finish	Anodized Black
------------------	----------------

.303 in

Primary Product Plating Material	Nickel
----------------------------------	--------

Primary Product Material	Aluminum Alloy
--------------------------	----------------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Configuration Features

Number of Fins	17
Number of Ports	1
Port Matrix Configuration	1 x 1

Product Type Features

Cage Type	Single
Thermal Accessory Type Included	Heat Sink
Form Factor	CFP2
Pluggable I/O Product Type	Cage Assembly
Sealable	Yes

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Other

Included Lightpipe	Yes
EMI Containment Feature Type	Internal/External EMI Springs
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2288221-1
CFP2 EMI/DUST PLUG



TE Part # 2274845-1
CFP2 RECEPTACLE ASSEMBLY



TE Part # 2215078-3
ASSY, STG TL, CFP2, 1X1 HS/LP


Customers Also Bought




TE Part #292304-2
STD USB TYPE B, R/A, T/H



TE Part #1625854-1
1206 PROBE PAD



TE Part #1-1586037-0
10P VERT HDR VAL-U-LOK V2



TE Part #1586037-8
8P VERT HDR VAL-U-LOK V2



TE Part #2274845-1
CFP2 RECEPTACLE ASSEMBLY



TE Part #2304452-1
RECEPTACLE COVER WITH GASKET,
CFP2 1X1



TE Part #2176340-3
CRGCQ 0603 2R2 5%



TE Part #2176341-1
CRGCQ 0805 10R 1%



Documents

Product Drawings

HARD WARE KITS WITH HS&LP,CFP2 1X1

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2314979-1_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2314979-1_B.3d_jgs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2314979-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English