

42KEHD10ABSD

✓ ACTIVE

Corcom KEH

TE Internal #: 2-1609969-3

42 A 3-Phase Filter, Terminal Block Input, Terminal Block Output, DELTA (3 wire + ground), 440 VAC, Chassis Mount, Corcom KEH

[View on TE.com >](#)



EMI & EMC Solutions > EMI Filters > Power Line Filters > 3-Phase Filters



Current Rating: 42 A

Input Termination Type: Terminal Block

Output Termination Type: Terminal Block

Wiring Configuration: DELTA (3 wire + ground)

Operating Voltage: 440 VAC

Features

Usage Conditions

Operating Temperature Range	-25 – 85 °C
-----------------------------	-------------

Product Type Features

Filtering Requirements	Filtered
Input Termination Type	Terminal Block
Output Termination Type	Terminal Block

Electrical Characteristics

Leakage Current (Max) (230VAC, 50Hz)	15
Current Rating	42 A
Operating Voltage	440 VAC

Configuration Features

Wiring Configuration	DELTA (3 wire + ground)
----------------------	-------------------------

Mechanical Attachment

Product Mount Type	Chassis Mount
--------------------	---------------

Other



EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Not Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-1609969-5
KEH 75A 2S SP DELTA BS 440VAC



TE Part # 2-1609969-4
KEH 55A 2S SP DELTA BS 440VAC



Also in the Series

Corcom KEH

3-Phase Filters(38)

Customers Also Bought

TE Part #CAT-T3437-H99
HX-SCE Low Fire Hazard Sleeves

TE Part #1-1337414-0
N Str Jk Hex 50Ohm Silver Pltd PSF 1 /4M,

TE Part #2-1622796-6
YR1 0.1% 42K2

TE Part #0462-209-16141
SOC, SOLID, SIZE 16, 14AWG, NI

TE Part #CN9926-000
SBP100375WE2.5

TE Part #1-1337415-0
N Str Plg Hex 50Ohm Silver Pltd RG9B /U,

TE Part #4-1622796-2
YR1 0.1% 97K6

Documents

Product Drawings

KEH 42A 2S SP DELTA BS 440VAC

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-1609969-3_B1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1609969-3_B1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2-1609969-3_B1.2d_dxf.zip

English

3D PDF



3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

KEH-BS SERIES

English