



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **32**

Number of Rows: **4**

Features

Electrical Characteristics

Operating Voltage	60 VDC
-------------------	--------

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
Connector Width	11.94 mm[.47 in]
PCB Thickness (Recommended)	1.35 mm[.053 in]
Connector Height	12.7 mm[.5 in]
Connector Length	66.55 mm[2.62 in]

Packaging Features

Packaging Quantity	33
Packaging Method	Tray

Industry Standards

Glow Wire Rating	High Temperature Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Usage Conditions

Operating Temperature (Max)	125 °C[257 °F]
Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]

Mechanical Attachment

Mating Retention	Without
------------------	---------



Mating Alignment Type	Polarization
PCB Mount Retention Type	Hold-Down
PCB Mount Alignment Type	Hold-Down
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Termination Features

Termination Post & Tail Length	3.43 mm[.135 in]
Termination Method to PCB	Through Hole - Press-Fit

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 – 2.54 µm[50 – 100 µin]
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
PCB Contact Termination Area Plating Material Thickness	2.54 – 5.08 µm[100 – 200 µin]
Contact Layout	Matrix
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material	Gold
Contact Type	Receptacle
Contact Current Rating (Max)	42 A

Housing Features

Housing Material	High Temperature Thermoplastic Glass-Filled
Centerline (Pitch)	5.08 mm[.2 in]

Configuration Features

Number of Columns	14
Number of Loaded Positions	32
Mating & Unmating Configuration	Normal
Number of Signal Positions	24
Number of Power Positions	8
PCB Mount Orientation	Vertical
Number of Positions	32



Number of Rows

4

Product Type Features

Mixed & Hybrid Header	Yes
Connector Shape	Rectangular
PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	Black
-----------------------	-------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these




limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 6-6450830-1
MBXL R/A HDR
3HDP+1LP+24S+1LP+3HDP

Also in the Series | MULTI-BEAM XLE



Board-to-Board Headers & Receptacles(99)




PCB Headers & Receptacles(99)



Rectangular Power Connectors(12)

Customers Also Bought




TE Part #2304452-1
RECEPTACLE COVER WITH GASKET, CFP2 1X1



TE Part #6123001-4
0.8FH,P08H.5,100,30/Sn,TR,SC



TE Part #6368460-4
INV MJ,1X2,PNL GRD,SHLD,LED (Y/G)



TE Part #2299805-3
NRW BACK PLATE ASSY,SOCKET P0, STUD7.74MM



TE Part #104501-1
PDBB 125 F2 Bus Bar PDS W/GDE

TE Part #2204145-3
MBXLE R/A RCPT 3ACP + 8P + 26S

TE Part #2274843-6
CAGE ASSY WITHOUT REAR SPRING,
CFP2 1X1

TE Part #2-6450820-7
MBXL VERT HDR 1P+16S+1P

TE Part #2016623-2
1.0-2.3 BULKHEAD TO UMCC WITH
1.37MM WH

TE Part #2170453-1
SFP+ 1x4 Cage Assy, with Heatsink

Documents

Product Drawings
MBXLE VERT RCPT 3HDP+1LP+24S+1LP+3HDP
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5-6450860-0_J.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_5-6450860-0_J.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_5-6450860-0_J.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Application Specification
English

Agency Approvals
UL Report
English