



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **General Purpose Resistor**

Element Type: **Thin Film**

Power Rating: **.6 W**

Resistance Class: **1MΩ – 1GΩ**

Resistance Value: **1M Ω**

Features

Usage Conditions

Operating Temperature Range	-55 – 155 °C
Temperature Coefficient	±50 ppm/°C

Electrical Characteristics

Operating Voltage	350 V
Power Rating	.6 W
Resistance Class	1MΩ – 1GΩ
Resistance Value	1M Ω
Passive Component Tolerance	1 %

Product Type Features

Resistor Type	General Purpose Resistor
Element Type	Thin Film

Configuration Features

Number of Resistors	1
---------------------	---

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2



Dimensions

Passive Component Dimensions	6.2 x 2.3 mm
------------------------------	--------------

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

LR1F1M0

Through-Hole General Purpose Resistor, Thin Film, .6 W, 1M ohm, 1 %, ±50 ppm/°C, Axial-Leaded, Copper Termination, 6.2 x 2.3 mm, Ammo Packed, Neohm LR



TE Part # 1622734-1
LR2 1% 33K



TE Part # 1622422-1
LR1 1% 2M2



TE Part # 1622733-1
LR2 1% 330R



TE Part # 1622170-1
LR0204 1% 16R



TE Part # 1622584-2
LR1 1% 8K45



TE Part # 1-1622318-5
LR1 1% 147K



TE Part # 1622585-1
LR1 1% 8K66



TE Part # 1622211-1
LR0204 1% 2K7



TE Part # 1622715-1
LR2 1% 22R



TE Part # 1622458-1
LR1 1% 39R



TE Part # 1614986-1
LR0204 1% 120R



TE Part # 1622511-1
LR1 1% 51R



TE Part # 1622526-1
LR1 1% 5K1



TE Part # 1622784-1
LR2 1% 820R



TE Part # 1622454-1
LR1 1% 390R



TE Part # 1622203-1
LR0204 1% 24R



TE Part # 1622242-1
LR0204 1% 47K



TE Part # 1622706-1
LR2 1% 1K8



TE Part # 1622277-1
LR0204 1% 75K



TE Part # 1622320-1
LR1 1% 150K

Also in the Series | [Neohm LR](#)



[DIMM Sockets\(5\)](#)




[Through-Hole Resistors\(490\)](#)


Customers Also Bought



TE Part #9-1419111-8
[PT571730](#)



TE Part #2-1879663-7
[H8 200R 0.1% 15PPM](#)




TE Part #2-1879664-4
[H8 2K0 0.1% 15PPM](#)



TE Part #330827
[TERMINAL,SOLIS SPD 16-14 6](#)



TE Part #2-1623720-9
[CCR2 15K 10%](#)



TE Part #7-1879665-3
[H8 69K8 0.1% 15PPM](#)




TE Part #1622796-7
[YR1 0.1% 115K](#)



TE Part #4-1879026-5
[YR1 0.1% 274K](#)



TE Part #8-1676913-3
[YR1 0.1% 30K9](#)



TE Part #1-1879666-6
[H8 191K 0.1% 15PPM](#)

Documents

Product Drawings

[LR1 1% 1M0](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_1622367-1_BA.2d_dxf.zip](#)

LR1F1M0

Through-Hole General Purpose Resistor, Thin Film, .6 W, 1M ohm, 1 %, ±50 ppm/°C, Axial-Leaded, Copper Termination, 6.2 x 2.3 mm, Ammo Packed, Neohm LR



English

Customer View Model

[ENG_CVM_CVM_1622367-1_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1622367-1_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1309350_PASSIVE_COMPONENT](#)

English

[Metal Film Fixed Resistors - Type LR series](#)

English