



TE Internal #: 5645945-1
Socket Length 4.01 mm [.158 in], PCB Hole Diameter 1.07 mm [.042 in], Bullet Nose, .102 – .205 mm² Wire, 27 – 24 AWG, Cable-to-Board, Pin Sockets
[View on TE.com >](#)

Connectors > Socket Connectors > Pin Sockets > Miniature Spring Sockets: Bullet Nose, Beryllium Copper, 4A



Socket Length: 4.01 mm [.158 in]
PCB Hole Diameter: 1.07 mm [.042 in]
Socket Sleeve Style: Bullet Nose
Wire Size: 27 – 24 AWG

[All Miniature Spring Sockets: Bullet Nose, Beryllium Copper, 4A \(14\)](#)

Features

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Method to Wire & Cable	Solder
Insertion Method	Hand/Semi-Automatic/Automatic

Body Features

Sleeve Plating Material	Tin
Sleeve Material	Copper

Packaging Features

Packaging Method	Loose Piece, Bag
Packaging Quantity	2000

Other

Spring Material	Beryllium Copper
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Operation/Application

Solder Process Feature	None
Circuit Application	Power & Signal



Contact Features

Contact Spring Plating Material	Tin
Contact Base Material	Beryllium Copper
Contact Mating Area Plating Material Thickness	2.54 µm
Contact Spring Plating Thickness	2.54 µm[30 µin]
Contact Current Rating (Max)	4 A

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Socket Sleeve Style	Bullet Nose
Connector System	Cable-to-Board
Sealable	No

Dimensions

PCB Thickness (Recommended)	.79 – 3.18 mm[.031 – .125 in]
Socket Length	4.01 mm[.158 in]
PCB Hole Diameter	1.07 mm[.042 in]
Wire Size	27 – 24 AWG
Mating Pin Diameter Range	.38 – .53 mm[.015 – .021 in]

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5645945-2
[SKT,MIN-SPR B-N SN-AU SER-1.5](#)

Customers Also Bought




TE Part #1393803-9
[V23100V6003A201](#)



TE Part #828296-8
[8P MOD 2 STIFT LEI](#)



TE Part #5645947-1
[SOCKET,MIN-SPR B-N SN-SN SER-1](#)



TE Part #7-1462039-4
[IM07DJR=IM RELAY 200mW 24V](#)



TE Part #6-2176374-0
[RQ 0805 442R 0.1% 10PPM 1K RL](#)



TE Part #1-1761692-3
[IDC LOW PRO HDR 40P RA LG LAT](#)



TE Part #2-829822-0
[2X20P MOD2 STIFTLEI](#)



TE Part #7-1393788-6
[V23079G1001B301](#)



Documents

Product Drawings

SKT,MIN-SPR B-N SN-SN SER 1.5

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5645945-1_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5645945-1_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5645945-1_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English