




Connectors > D-Shaped Connectors > Microminiature & Nanominiature D Connectors > DUALOBE Receptacle Connectors: Metal Shell, 51 Pin/2 row



Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **51**

Centerline (Pitch): **.64 mm [.025 in]**

Sealable: **No**

[All DUALOBE Receptacle Connectors: Metal Shell, 51 Pin/2 row \(11\)](#)

Features

Contact Features

Contact Type	Socket
Contact Options	Installed

Termination Features

Termination Method to PCB	Surface Mount
Termination Method to Wire & Cable	Preterminated Flying Leads

Product Type Features

Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Positions	51
---------------------	----

Housing Features

Centerline (Pitch)	.64 mm[.025 in]
--------------------	-----------------

Operation/Application

Circuit Application	Power
---------------------	-------



Other

EU RoHS Compliance	Not Compliant
EU ELV Compliance	Not Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) SVHC > Threshold: Pb (40% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1589666-5
302-0009-02 = CLEADFRAME

Customers Also Bought

TE Part #HPP845E031R4
I.C 21D RH/T B400

TE Part #2347330-1
2MM HM FEMALE ASSY, COL8

TE Part #34853
TERMINAL,PG R 12-10 8

TE Part #1623156-1
CRG0805 1% 220R

TE Part #1676209-2
RN 0805 17K8 0.1% 10PPM 1KRL

TE Part #4-1617002-1
B07B035BC1 = B07 10 AMP RELAY

TE Part #005087-000
202D153-4/86-0

TE Part #680333-000
D-609-13

TE Part #2-320561-2
TERMINAL,PIDG R 16-14 6

TE Part #430328-000
202C621-51/164-0

Documents

Product Drawings
STM051L2AQ = SMT CONN
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_6-1589483-0_U_c-6-1589483-0-u.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_6-1589483-0_U_c-6-1589483-0-u.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_6-1589483-0_U_c-6-1589483-0-u.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1589483 Nanonics Cross Reference](#)

English