

3-2106003-2 ACTIVE

LUMAWISE | Insulation Displacement Connectors Closed End

TE Internal #: 3-2106003-2

Wire-to-Board, 2 Position, .16 mm [4 in] Centerline, Printed Circuit Board, Insulation Displacement Connectors Closed End, Poke-In Connectors

[View on TE.com >](#)



Connectors > Lighting Connectors > Poke-In Connectors



Connector System: **Wire-to-Board**

Number of Positions: **2**

Centerline (Pitch): **.16 mm [4 in]**

Connector & Contact Terminates To: **Printed Circuit Board**

Connector Height: **.23 mm [5.8 in]**

Features

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Product Type Features

Connector System	Wire-to-Board
------------------	---------------

Connector & Contact Terminates To	Printed Circuit Board
-----------------------------------	-----------------------

Configuration Features

Number of Positions	2
---------------------	---

Contact Features

Contact Current Rating (Max)	6 A
------------------------------	-----

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Housing Features

Centerline (Pitch)	.16 mm[4 in]
--------------------	--------------

Dimensions

Connector Height	.23 mm[5.8 in]
------------------	----------------

Wire Size	24 – 22 AWG
-----------	-------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Other

EU RoHS Compliance	Compliant
--------------------	-----------

EU ELV Compliance	Compliant
-------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------

EU ELV Directive 2000/53/EC	Compliant
-----------------------------	-----------

China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
---	---

EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241)
--	---

Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
-----------------	---

Solder Process Capability	Wave solder capable to 265°C
---------------------------	------------------------------

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 7-2106003-2
Connector, SMT-IDC, 2 pos, 24AWG,
black




TE Part # 3-2106431-2
Connector, SMT-IDC PASS THRU, 2
POS, 24AWG

Also in the Series | Insulation Displacement Connectors Closed End




Ballast Connectors(16)




Board-In Connectors(9)



PCB Headers & Receptacles(1)



Poke-In Connectors(66)



Wire-to-Board Headers & Receptacles
(1)

Customers Also Bought



TE Part #1445022-5
MICRO MNL RFECEPT HSG SINGLE R



TE Part #4-1393240-5
RT334012



TE Part #2-1437565-9
FSM2JSMATTR=TACTILE 260G
FORCE



TE Part #640445-2
02P MTA156 HDR ASSY FL/STR SN



TE Part #1445049-6
FREE HANG SNGL ROW HSG 6 POS



TE Part #9-1879333-0
CPF0402 180K 0.1% 25PPM 5K RL



TE Part #9-2176306-1
RP 1E 0.1W 10K 0.1% 25PPM 5K RL



TE Part #2232043-3
3P, RAST 5 Tab Header, THV

TE Part #881545-2
SHUNT LP W/HANDLE 2 POS 30AUTE Part #2-1977223-4
FSM8JSMASTR=6MM TACT SWITCH,
SMT 160gf,

Documents

Product Drawings

Connector, SMT-IDC, 2 POS, 24 AWG

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_3-2106003-2_B.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-2106003-2_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-2106003-2_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

IDC_SSL_CONNECTOR

English

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English