

532782-1

✓ ACTIVE


AMP-HDI

TE Internal #: 532782-1

Keying Insert, Stainless Steel

[View on TE.com >](#)

Connectors > Connector Accessories > Connector Hardware

Connector Hardware Accessory Type: **Keying Insert**Primary Product Material: **Stainless Steel**Operating Temperature (Max): **105 °C [221 °F]**Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**Hardware Accessory Function: **Coding & Keying**

Features

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Type Features

Connector Hardware Accessory Type	Keying Insert
Hardware Accessory Function	Coding & Keying

Body Features

Primary Product Material	Stainless Steel
--------------------------	-----------------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance




For compliance documentation, visit the product page on [TE.com](https://www.te.com)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

 TE Part #3-338309-2 9POS.HD20 PLUG ASSY	 TE Part #42037 RING TERMINAL 22-18 AWG TPBR	 TE Part #8-1879214-0 CPF 0402 2K49 0.1% 25PPM 1K RL	 TE Part #1617123-4 JMAP-26XL = M39016/9-024L
 TE Part #3-2176244-7 CRGS0805 5% 1K0	 TE Part #532448-6 HDI PIN ASSY 4 ROW 180 POS	 TE Part #9148732002 RNF-3000-18/6-9-STK	 TE Part #531713-1 BOX GUIDE/KEYING PIN



Documents

Product Drawings

HDI GUIDE/KEYING INSERT

English

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_532782-1_H.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_532782-1_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_532782-1_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

[Application Specification](#)

English