



TE Internal #: 1-61795-0
Closed Ring Tongue Terminal, 18 – 14 AWG, #10 Stud, 7.75 mm [.305 in] Stud Diameter, Open Barrel, Straight, Tin Plating, Uninsulated
[View on TE.com >](#)

Terminals & Splices > Ring Terminals



Ring Terminal Product Type: Closed Ring Tongue Terminal

Wire Size: .8 – 2.08 mm²
Stud Size: #10
Stud Diameter: 7.75 mm [.305 in]

Features

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Contact Features

Contact Base Material	Brass
Barrel Type	Open
Terminal Orientation	Straight
Terminal Plating Material	Tin
Contact Underplating Material	None

Dimensions

	.105 in
Wire Size	.8 – 2.08 mm²
Stud Diameter	7.75 mm [.305 in]
Tongue Thickness	.51 mm [.02 in]
Product Length	19.56 mm [.77 in]

Product Type Features

Shape Description	Anti-Rotational/Grounding
-------------------	---------------------------



Ring Terminal Product Type	Closed Ring Tongue Terminal
Stud Size	#10
Sealable	No
Compatible With Discrete Wire Type	Stranded
Wire Insulation Support Retention Type	Non-Insulation Support

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Strip/Reel
------------------	------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability









Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part












numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 <p>TE Part # 61435-1 RING 18-14 AWG .020 X .500 BR</p>	 <p>TE Part # 1-61795-1 RING 18-14 AWG TPBR</p>	 <p>TE Part # 34839 RING TERMINAL 18-14 AWG BR</p>	 <p>TE Part # 190225-2 RING I/S PRE TIN BRASS</p>
 <p>TE Part # 40594 RING TERMINAL 18-14 AWG TPBR</p>	 <p>TE Part # 61795-3 RING 18-14 AWG TPBR</p>	 <p>TE Part # 40595 RING TERMINAL 18-14 AWG TPBR</p>	 <p>TE Part # 40593 RING 18-14 6 .020 TPBR</p>

Customers Also Bought

 <p>TE Part #2-1744036-6 06P ECONOMY POWER .200 CL HSG</p>	 <p>TE Part #1969608-3 3P VAL-U-LOK TPA 22-18 AWG</p>	 <p>TE Part #1-1969443-3 EP 2.5 TPA Retainer, 13 Pos</p>	 <p>TE Part #1969608-1 1P VAL-U-LOK TPA 22-18 AWG</p>
 <p>TE Part #521229-1 PL 250 HOUSING RECEPTACLE NYLON 6/6</p>	 <p>TE Part #1969612-2 2P FH PLUG VAL-U-LOK V0</p>	 <p>TE Part #63678-2 RING 18-14 AWG TPBR</p>	 <p>TE Part #1969612-4 4P FH PLUG VAL-U-LOK V0</p>



Documents

Product Drawings

RING 18-14 105-145 #10 025TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-61795-0_BB.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-61795-0_BB.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-61795-0_BB.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.