




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **509 – 1900 CMA**

Mating Tab Width: **2.79 mm [.11 in]**

Features

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Connection Capacity	Single
---------------------	--------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Electrical Characteristics

Voltage Rating	300 V
----------------	-------

Body Features

Insulation Material	Nylon
---------------------	-------

Other

Barrel Color	Transparent
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Type Features

--	--



Terminal Features	Wire Stop
Insertion Force	Normal

Packaging Features

Packaging Quantity	100
Packaging Method	Loose Piece

Dimensions

Product Length	18.64 mm[.734 in]
Compatible Insulation Diameter Range	2.54 mm[.1 in]
Terminal Material Thickness	.3 mm[.012 in]
Wire Size	509 – 1900 CMA

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	2.79 mm[.11 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Pre-Tin
Crimp Type	Compression Crimp
Barrel Type	Closed

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

REPRESENTATION ONLY

TE Part # 90185-1
DAHT PIDG FASTON 22-18 ASSY

Also in the Series | FASTON 110

Crimp Terminal Housings(13)

Insertion & Extraction Tools(1)

PCB Terminals(22)

Quick Disconnects(168)

Customers Also Bought

TE Part #6-102398-1
26 AMPMODU MT ASSY DR .100CL

TE Part #CAT-P592-R472A
PIDG Ring Tongue Terminals

TE Part #EK4903-000
BTH1-25-16-1-ZN-SB

TE Part #801953-000
TXR21AB00-1408AI



TE Part #AAB1895-00
[91H1-15-10-1-C-HE200](#)

TE Part #AAB2058-00
[91H1-17-12-1-C-HE300](#)

TE Part #AAB2145-00
[91H1-19-08-1-C-HE200](#)

TE Part #AAB2273-00
[91H1-21-08-1-C-HE200](#)



TE Part #166294-1
[20DF CRIMP PIN](#)

Documents

Product Drawings

[RECEPT,PIDG FASTON 22-18 110](#)

English

CAD Files

[3D PDF](#)

English

Customer View Model

[ENG_CVM_8-61060-1_N1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_8-61060-1_N1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_8-61060-1_N1.3d_stp.zip](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_8-61060-1_U.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-61060-1_U.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-61060-1_U.3d_stp.zip](#)

English



By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

APPLICATION AND MAINTENANCE FOR CRIMPING HEAD ASSEMBLY 90386-1

English

Agency Approvals

CSA Certificate

English