



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **80**

Centerline (Pitch): **.8 mm [.031 in]**

Features

Electrical Characteristics

Operating Voltage	125 VAC
Impedance	100 Ω
Insulation Resistance	2 MΩ
Dielectric Withstanding Voltage (Max)	675 VAC

Dimensions

	.136 in
Stack Height	8 mm, 30 mm, 19 mm, 22 mm, 5 mm, 25 mm, 16 mm, 11 mm[1.181 in]
Connector Height	3.05 mm[.12 in]

Packaging Features

Packaging Quantity	56
Packaging Method	Tray, Box

Body Features

Assembly Process Feature Material	Polyimide Film
-----------------------------------	----------------



Primary Product Color	Black
-----------------------	-------

Operation/Application

Assembly Process Feature	Pick and Place Cover
Circuit Application	Power & Signal

Mechanical Attachment

Mating Retention	With
PCB Mount Alignment Type	Locating Posts
PCB Mount Retention	With
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	Without

Termination Features

Rectangular Termination Post & Tail Width	1.77 mm[.07 in]
Rectangular Termination Post & Tail Thickness	.15 mm[.006 in]
Termination Method to PCB	Surface Mount

Contact Features

	29.9212 μin
Mating Tab Width	.38 mm[.015 in]
PCB Contact Termination Area Plating Material Thickness	.76 μm[29.9212 μin]
Contact Shape & Form	Single Beam
Contact Base Material	Phosphor Bronze
Mating Tab Thickness	.2 mm[.008 in]
PCB Contact Termination Area Plating Material	Gold
Contact Mating Area Plating Material	Gold
Contact Type	Socket
Contact Current Rating (Max)	1.25 A, 9.5 A

Housing Features

Housing Material	LCP (Liquid Crystal Polymer)
Centerline (Pitch)	.8 mm[.031 in]

Configuration Features

Connector Contact Load Condition	Fully Loaded
Board-to-Board Configuration	Parallel



Stackable	No
PCB Mount Orientation	Vertical
Number of Positions	80

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
Connector System	Board-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Usage Conditions

Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

















Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


			
TE Part # 1658017-2 MSB0.80PL19ASY080FL,-,10,-TY	TE Part # 2-1658464-2 MSB0.80PL8ASY080FL,-,30,-TY	TE Part # 4-1658013-2 MSB0.80PL5ASY080FL,GP,10,-TR	TE Part # 4-1658463-2 MSB0.80PL5ASY080FL,GP,30,-TR
			
TE Part # 6-1658463-2 MSB0.80PL5ASY080FL,GP,30,-TR	TE Part # 6-1658466-2 MSB0.80PL16ASY080FL,GP,30,-TR	TE Part # 4-1658045-2 MSB0.80PL8ASY080FL,GP,F,-TR	TE Part # 4-1658014-2 MSB0.80PL8ASY080FL,GP,10,-TR
			
TE Part # 2-1658439-2 MSB0.80PL14ASY080FL,-,30,-TY	TE Part # 1658468-2 MSB0.80PL22ASY080FL,-,30,-TY	TE Part # 1658469-2 MSB0.80PL25ASY080FL,-,30,-TY	TE Part # 1658438-2 MSB0.80PL14ASY080FL,-,10,-TY
			
TE Part # 1658045-2 MSB0.80PL8ASY080FL,-,F,-TY	TE Part # 1658048-2 MSB0.80PL19ASY080FL,-,F,-TY	TE Part # 1658013-2 MSB0.80PL5ASY080FL,-,10,-TY	TE Part # 1658018-2 MSB0.80PL22ASY080FL,-,10,-TY




TE Part # 4-1658465-2
[MSB0.80PL11ASY080FL,GP,30,-TR](#)



TE Part # 6-1658047-2
[MSB0.80PL16ASY080FL,GP,F,-TR](#)



TE Part # 6-1658015-2
[MSB0.80PL11ASY080FL,GP,10,-TR](#)




TE Part # 6-1658013-2
[MSB0.80PL5ASY080FL,GP,10,-TR](#)

Customers Also Bought



TE Part #1-1318301-2
[3.96EP HDR ASSY 2\(3\)P NAT/TUBE](#)



TE Part #5103311-8
[A/L LOW PRO HDR 40P RA BLACK](#)

Documents

Product Drawings

[MSB0.80RC-ASY080FL,-,30,-TY](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_2-1658462-2_L_c-2-1658462-2-l.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1658462-2_L_c-2-1658462-2-l.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2-1658462-2_L_c-2-1658462-2-l.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[MICTOR SB Interconnection System](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals



[UL Report](#)

English