



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Base Housing**

Cable Entry Location: **Bottom**

Hood & Base Locking Device Type: **Screwlock**

Sealable: **Yes**

EU RoHS Compliance: **Compliant**

Features

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Product Type Features

Hood & Base Connector Product Type	Base Housing
Sealable	Yes

Body Features

Cable Entry Location	Bottom
----------------------	--------

Mechanical Attachment

Hood & Base Locking Device Type	Screwlock
---------------------------------	-----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2022 (223) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # T2010032201-000  
HA-003-F



TE Part # T1927031120-000  
H3APR-MTGSW-M20

Customers Also Bought



TE Part #1-1393239-6  
RT114110



TE Part #770010-3  
UMNL II SOK PTPPHBZ



TE Part #BSA896N0085056A000  
917 PLUG, SPEEDTEC



TE Part #T2020072101-000  
HD-007-M




TE Part #9395153002  
FLHTC0311-26-1




TE Part #T1927031120-000  
H3APR-MTGSW-M20



TE Part #T1937031000-000  
H3APR-MAGSW



TE Part #1SNA002351R0500  
TB ASSY-ABB SACE-164791-GR.804



TE Part #5-163081-4  
.062 DIA PIN ASSY 3+ WITH SPL  
PACKAGING



TE Part #T1902241232-100  
H24BPR-TS/GHC-2M32

Documents

Product Drawings

H3APR-MAGS

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_T1946031000-000\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_T1946031000-000\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_T1946031000-000\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Heavy Duty Connectors

English

Product Specifications

Application Specification

English