

Kemtron | Kemtron 1202 Series

TE Internal #: 2418219-1

Extruded EMI Gasket, Conductive Strip, Fluorosilicone Binding,  
Silver Plated Aluminum (Ag/Al) Filler, Tube, Length 10 m [32.8 ft],  
Kemtron 1202 Series

[View on TE.com >](#)

EMI & EMC Solutions > EMI Shielding > EMI Gaskets > Extruded EMI Gasket Conductive Strip



Gasket Type: Extruded EMI Gasket

Finished Type: Conductive Strip

Binding Material: Fluorosilicone

Filler Material: Silver Plated Aluminum (Ag/Al)

Gasket Shape: Tube

[All Extruded EMI Gasket Conductive Strip \(56\)](#)

## Features

### Body Features

Gasket Type	Extruded EMI Gasket
Gasket Shape	Tube

### Product Type Features

Finished Type	Conductive Strip
Binding Material	Fluorosilicone
Filler Material	Silver Plated Aluminum (Ag/Al)

### Dimensions

Product Length	10 m[32.8 ft]
Outside Diameter	1.6 mm[.062 in]
Inside Diameter	.5 mm[.019 in]

### Usage Conditions

Operating Temperature Range	-55 – 160 °C[-67 – 320 °F]
-----------------------------	----------------------------

### Electrical Characteristics

Resistance to Petroleum	Yes
Volume Resistivity (Max)	.012 Ω.cm

### Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

### Product Compliance

For compliance documentation, visit the product page on [TE.com](http://TE.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: DCP (.32% in Component)
Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Compatible Parts




TE Part # CAT-EMIG-0001  
Extruded EMI Gasket Conductive Strip



TE Part # 2452644-1  
SNA Tube 1.6mm OD x 0.5mm ID x 10m L

## Also in the Series | Kemtron 1202 Series



EMI Gaskets(36)



Medical EMI & EMC Solutions(36)

## Customers Also Bought




TE Part #CAT-R21-731072  
Bulbous Heat Shrink Boots: Lipped, Straight



TE Part #CAT-T3437-R819  
RPS Commercial Grade Sleeves



TE Part #820192-000  
382A012-25-0



TE Part #391025-000  
462A011-100-0



TE Part #5053032054  
RNF-100-1/8-9-STK



TE Part #6641710001  
TMS-SCE-1/4-2.0-9



TE Part #5960092001  
TFER-1-1/4-X-STK

## Documents

### Product Drawings

[FSA Tube 1.6mm OD x 0.5mm ID x 10m L](#)

English

### Datasheets & Catalog Pages

[Performance Materials brochure](#)

English

**Datasheet - Conductive Elastomers**

English

---

**Product Specifications**

**Application Specification**

English