



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **2**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-2**

Features

Packaging Features

Packaging Quantity	100
--------------------	-----

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Product Type Features

Connector & Contact Terminates To	Wire & Cable
Sealable	No
Connector System	Wire-to-Board, Wire-to-Wire
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	2
---------------------	---

Body Features

--	--



Primary Product Color	Black
-----------------------	-------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without

Housing Features

Housing Material	Nylon
Centerline (Pitch)	6 mm[.236 in]

Usage Conditions

Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part




numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 170234-1
POSITIVE LOCK RECP



TE Part # 928083-1
PL 187 REC HSG 1P NYLON NAT




TE Part # 170233-1
PL 250 REC 0.5-2.27 MM2 BR



TE Part # 926716-1
PL 2P HOUSING PA 6.6 ZYTEL 101
BLACK

Also in the Series | Positive Lock 250



Automotive Terminals(1)



Crimp Terminal Housings(184)



Insertion & Extraction Tools(3)



Insulation Boots & Sleeves(4)



Quick Disconnects(185)

Customers Also Bought



TE Part #CAT-EC7491-CH8172
ECONOSEAL, CONNECTOR
HOUSING




TE Part #174662-7
12 POS PLUG MARK II+




TE Part #7-1622796-4
YR1 0.1% 169R



TE Part #5-1676913-3
YR1 0.1% 255R




TE Part #174664-7
12 POS DL PLATE FOR CAP MKII+



TE Part #1-174258-1
E-J MK-2 PLUG HSG 4P NATURAL



TE Part #2005563-2
PCU 196P COVER HSG TYPE C



TE Part #176118-6
070 MLC II PLUG ASSY 18P GRAY



TE Part #172508-1
MIC CAP HSG 13P MK II

Documents

Product Drawings

POSITIVE LOCK HOUSING RECEPTACLE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_171810-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_171810-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_171810-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Crimping of Positive Lock Receptacle Contact

English

Application Specification

English

Agency Approvals

UL Report

English

171810-2

Receptacle, Receptacle, 2 Position, Straight, UL 94V-2, Black, Nylon, Cable Mount
(Free-Hanging), Positive Lock 250, Crimp Terminal Housings

