




Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Primary Product Color: **Black**

Primary Product Material: **Nylon**

Number of Positions: **36**

Operating Temperature (Max): **130 °C [266 °F]**

Features

Industry Standards

Compatible With Agency/Standards Products	UL, VDE, CSA
---	--------------

Mechanical Attachment

Strain Relief	With
---------------	------

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Type Features

Sealable	No
Connector Cover Type	Strain Relief Cover

Body Features

Primary Product Color	Black
Primary Product Material	Nylon

Configuration Features

Number of Positions	36
---------------------	----

Usage Conditions

Operating Temperature (Max)	130 °C[266 °F]
Operating Temperature Range	-55 – 130 °C[-67 – 266 °F]

Other



EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | AMP Metrimate



Connector Caps & Covers(4)

Connector Hardware(4)

Insertion & Extraction Tools(1)

PCB Headers & Receptacles(80)

Rectangular Connector Housings(34)

Rectangular Contact Inserts(4)

Wire-to-Board Headers & Receptacles (80)

Customers Also Bought

TE Part #929504-4
2X 5P JUN POW TIMGH

TE Part #2-179555-6
DYNAMIC D-3200 WTW TAB HSG 12P

TE Part #207601-1
METRIMATE,STR REL KIT,9P

TE Part #207442-1
18 POS SQ GRID METRIMATE-PLUG

TE Part #207305-1
24 POS SQ GRID METRIMATE-RCPT

TE Part #42282-2
FF 250 REC 18-14AWG TPBR LP

TE Part #180900
FF 250 REC HSG 4P NYLON NAT

TE Part #2829957-1
CA, Cust. communication RJ45 plug CAT5e

TE Part #826886-7
3P ECONOSEAL BU GEH

TE Part #827396-2
HYLSA PIC

Documents



Product Drawings

METRIMATE,STR REL KIT,36P

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_207604-1_D.3d_igs.zip

English

Customer View Model

ENG_CVM_207604-1_D.3d_stp.zip

English

Customer View Model

ENG_CVM_207604-1_D.2d_dxf.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

METRIMATE_PIN_SOCKET_CATALOG

English

Product Specifications

Application Specification

English

Application Specification

English

METRIMATE Self-Locking Connectors

Japanese

Application Specification

Japanese

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

CSA Certificate

English