



Passive Components > Resistors > Through-Hole Resistors



Resistor Type: **Power Resistor**
Element Type: **Metal Film**
Power Rating: **3 W**
Resistance Class: **Up to 1kΩ**
Resistance Value: **560 Ω**

Features

Electrical Characteristics

Operating Voltage	750 V
Power Rating	3 W
Resistance Class	Up to 1kΩ
Resistance Value	560 Ω
Passive Component Tolerance	5 %

Product Type Features

Resistor Type	Power Resistor
Element Type	Metal Film

Configuration Features

Number of Resistors	1
---------------------	---

Body Features

Lead Type	Axial-Leaded
-----------	--------------

Termination Features

Termination Area Base Material	Copper
Number of Terminations	2

Dimensions

Passive Component Dimensions	15 x 5 mm
------------------------------	-----------



Usage Conditions

Temperature Coefficient	±300 ppm/°C
-------------------------	-------------

Packaging Features

Packaging Method	Ammo Packed
------------------	-------------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

RR03J560RTB

Through-Hole Power Resistor, Metal Film, 3 W, 560 ohm, 5 %, ±300 ppm/°C, Axial-Leaded, Copper Termination, 15 x 5 mm, Ammo Packed, Neohm RR



TE Part # 6-1879354-6
RR03 5% 160R AMMO

TE Part # 5-1879352-5
RR02 5% 56R AMMO

TE Part # 8-1879354-5
RR03 5% 1K0 AMMO

TE Part # 4-1879350-9
RR01 5% 22R AMMO

TE Part # 7-1879352-7
RR02 5% 470R AMMO

Also in the Series | [Neohm RR](#)

[Through-Hole Resistors\(478\)](#)

Customers Also Bought

TE Part #813854-000
202A153-3-0

TE Part #9-1462037-9
IM06CGR=IM RELAY 140mW12V HDV

TE Part #9-2176231-5
3522 82K 1% 3W


TE Part #CONREV SMA012
RP-SMA RA Plug 50 Ohm PCB Cable Crimp

TE Part #CONSMA007
SMA Plug 50 Ohm Cable Crimp

TE Part #CONSMA012
SMA RA Plug 50 Ohm Cable Crimp

TE Part #1879354-5
RR03 5% R47 AMMO

TE Part #2-1393225-6
RY612012



Documents

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_7-1879354-9_BA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-1879354-9_BA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-1879354-9_BA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[4-1773460-6_RESISTIVE_SOLUTIONS_RAIL](#)

English

[1309350_PASSIVE_COMPONENT](#)

English

[Power Resistor - Type RR Series - Tyco Electronics Passives](#)

English

[8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS](#)

English