




Connectors > Circular Connectors > DIN Connectors



Circular DIN Connector Type: **Mini DIN**

Connector System: **Wire-to-Board**

Number of Positions: **6**

Connector Contact Load Condition: **Fully Loaded**

Mating Alignment Type: **Polarization**

Features

Electrical Characteristics

Operating Voltage	30 VAC
-------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Termination Features

Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.18 mm[.125 in]

Dimensions

Product Width	17.78 mm[.7 in]
Product Length	22.61 mm[.89 in]
PCB Thickness (Recommended)	2.68 mm[.11 in]
Connector Height	13.08 mm[.51 in]

Body Features

Shield Plating Thickness	3.81 μm, 5.08 μm[200 μin][150 μin]
Shield Plating Finish	Bright
Shield Plating Material	Tin over Nickel



Shield Material	Brass
Shield Underplate Material	Nickel
Panel Ground Feature Type	Flange
Primary Product Color	Black
Shield Underplate Thickness	1.27 µm[50 µin]

Packaging Features

Packaging Quantity	24
Packaging Method	Tube

Operation/Application

Shielded	Yes
Circuit Application	Signal

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Shape & Form	Tuning Fork
PCB Contact Termination Area Plating Material Thickness	3.81 µm, 2.54 µm[150 µin][100 µin]
Contact Layout	Staggered
Contact Mating Area Plating Material	Gold
Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
Contact Current Rating (Max)	.5 A

Housing Features

Housing Material	Thermoplastic
Centerline (Pitch)	6.5 mm[.26 in]

Mechanical Attachment

Panel Mount Feature	With
Panel Mount Feature Type	Screw Nut
Mating Alignment	With
PCB Mount Alignment	With
PCB Mount Alignment Type	Hold-Down



Mating Alignment Type	Polarization
PCB Mount Retention	With
PCB Mount Retention Type	Kinked Legs
Connector Mounting Type	Board Mount

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	6
Connector Contact Load Condition	Fully Loaded

Product Type Features

Circular DIN Connector Type	Mini DIN
Connector System	Wire-to-Board
Connector & Contact Terminates To	Printed Circuit Board

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part




numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #CAT-103156-WBHSM
Receptacle Housing: Wire-to-Board, with Mating Alignment, SL156




TE Part #170484-1
CONTACT FOR DRAWER CONNECTOR




TE Part #3-520140-2
ULTRA-FAST 250 ASY REC 16-14 AWG TPBR




TE Part #3-2176389-9
RQ 1206 267R 0.1% 10PPM 5K RL




TE Part #4-2176388-9
RQ 1206 31R6 0.1% 10PPM 5K RL




TE Part #5-2176388-8
RQ 1206 39R2 0.1% 10PPM 5K RL



TE Part #3-350980-1
SL156 RECEPTACLE



TE Part #1419106-4
27E046=SOCKET,KU,11,PC,NYL,NAT



TE Part #87165-1
LOCKING CLIP ASSY .025 SQ LP

Documents

- CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5750131-2_O.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5750131-2_O.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5750131-2_O.3d_stp.zip](#)



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English