

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Plug, nom. voltage: 800 V, nominal current: 32 A, number of positions: 1, connection method: Screw connection, Rated cross section: 4 mm², cross section: 0.2 mm²- 6 mm², color: blue

Product description

Connector element center, left housing with engagement pin, right opened without cover

Your advantages

- The COMBI plugs for self-assembly provide solutions that users can implement themselves
- The screw plugs can be combined with COMBI terminal blocks with all forms of connection technology and are available in two versions
- The plugs are assembled directly on site by snapping together 1-position plug elements
- The plug design enables space-saving potential distribution by using four-conductor terminal blocks with two slots

Commercial data

| | |
|--------------------------------------|---------------------|
| Item number | 3060063 |
| Packing unit | 50 pc |
| Minimum order quantity | 50 pc |
| Sales key | BE01 |
| Product key | BE1144 |
| Catalog page | Page 336 (C-1-2019) |
| GTIN | 4046356090186 |
| Weight per piece (including packing) | 5.191 g |
| Weight per piece (excluding packing) | 4.6 g |
| Customs tariff number | 85366990 |
| Country of origin | TR |

UP 4/ 1-M BU - Plug



3060063

<https://www.phoenixcontact.com/us/products/3060063>

Technical data

Product properties

| | |
|---------------------|---------------|
| Product type | Terminal plug |
| Number of positions | 1 |
| Pitch | 6.2 mm |
| Potentials | 1 |

Insulation characteristics

| | |
|---------------------|-----|
| Ovvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---------------------|------|
| Rated surge voltage | 8 kV |
|---------------------|------|

Connection data

| | |
|---|---|
| Nominal cross section | 4 mm ² |
| Screw thread | M3 |
| Tightening torque | 0.6 ... 0.8 Nm |
| Stripping length | 9 mm |
| Internal cylindrical gage | A4 |
| Connection in acc. with standard | IEC 61984 |
| Conductor cross section rigid | 0.2 mm ² ... 6 mm ² |
| Cross section AWG | 24 ... 10 (converted acc. to IEC) |
| Conductor cross section flexible | 0.2 mm ² ... 6 mm ² |
| Conductor cross section, flexible [AWG] | 24 ... 10 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.25 mm ² ... 4 mm ² |
| Flexible conductor cross section (ferrule with plastic sleeve) | 0.25 mm ² ... 4 mm ² |
| 2 conductors with same cross section, solid | 0.2 mm ² ... 1.5 mm ² |
| 2 conductors with same cross section, flexible | 0.2 mm ² ... 1.5 mm ² |
| 2 conductors with same cross section, flexible, with ferrule without plastic sleeve | 0.25 mm ² ... 1.5 mm ² |
| 2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve | 0.5 mm ² ... 1.5 mm ² |
| Nominal current | 32 A |
| Maximum load current | 32 A (with 6 mm ² conductor cross section) |
| Nominal voltage | 800 V |
| Nominal cross section | 4 mm ² |

Dimensions

| | |
|--------|---------|
| Width | 6.2 mm |
| Height | 21 mm |
| Depth | 41.2 mm |
| Length | 21 mm |
| Pitch | 6.2 mm |

UP 4/ 1-M BU - Plug



3060063

<https://www.phoenixcontact.com/us/products/3060063>

Material specifications

| | |
|---|-----------------|
| Color | blue (RAL 5015) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I |
| Insulating material | PA |
| Static insulating material application in cold | -60 °C |
| Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21)) | 125 °C |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R24 | HL 1 - HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R26 | HL 1 - HL 3 |
| Calorimetric heat release NFPA 130 (ASTM E 1354) | 27,5 MJ/kg |
| Surface flammability NFPA 130 (ASTM E 162) | passed |
| Specific optical density of smoke NFPA 130 (ASTM E 662) | passed |
| Smoke gas toxicity NFPA 130 (SMP 800C) | passed |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Ambient temperature (operation) | -60 °C (max. operating temperature see derating curve) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|-----------|
| Connection in acc. with standard | IEC 61984 |
|----------------------------------|-----------|

UP 4/ 1-M BU - Plug




3060063

<https://www.phoenixcontact.com/us/products/3060063>

Drawings

Schematic diagram




UP 4/ 1-M BU - Plug



3060063

<https://www.phoenixcontact.com/us/products/3060063>



Circuit diagram



UP 4/ 1-M BU - Plug



3060063

<https://www.phoenixcontact.com/us/products/3060063>

Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3060063>



CSA

Approval ID: 13631



IECEE CB Scheme

Approval ID: NL-34722_A1

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | 800 V | 32 A | - | - |



cULus Recognized

Approval ID: E60425



KEMA-KEUR

Approval ID: 71-114072 REV.1

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|--|-----------------------|-----------------------|-------------------|----------------------|
| | 800 V | 32 A | - | - |



CSA

Approval ID: 13631



EAC

Approval ID: EACKZ 08593



cULus Recognized

Approval ID: E60425

UP 4/ 1-M BU - Plug

3060063

<https://www.phoenixcontact.com/us/products/3060063>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27141151 |
| ECLASS-12.0 | 27141151 |
| ECLASS-13.0 | 27250306 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC002021 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

UP 4/ 1-M BU - Plug

3060063

<https://www.phoenixcontact.com/us/products/3060063>



Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com