




Terminals & Splices > Spade Terminals



Spade Terminal Type: **Spade Tongue Terminal**

Wire Size: **2050 – 5180 CMA**

Stud Size: **#6, M3.5**

Features

Body Features

Product Weight	.539 g
----------------	--------

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Industry Standards

Government Qualified Terminal	No
-------------------------------	----

Packaging Features

Packaging Quantity	5000
Packaging Method	Tape Mounted

Product Type Features

Stud Size	#6, M3.5
Sealable	No
Wire Insulation Support Retention Type	Non-Insulation Support

Contact Features

Spade Terminal Type	Spade Tongue Terminal
Barrel Type	Closed



Terminal Orientation	Straight
Terminal Plating Material	Tin

Dimensions

Wire Size	2050 – 5180 CMA
Stud Diameter	3.68 mm[.145 in]
Tongue Thickness	.79 mm[.031 in]
Product Length	13.46 mm[.53 in]
Barrel Inside Diameter	2.16 mm[.085 in]

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Operation/Application

Compatible With Wire Base Material	Copper
Compatible With Wire Plating Material	Tin

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58545-3  
SDE DIE ASSY. 22-10 SOLISTRAND

TE Part # 58545-1  
SOLISTRAND 10-22 DIE ASSY

TE Part # 49935  
DAHT SOLIS 22-10 ASSY

TE Part # 58546-1  
PC 22-10 SOLISSPICE SPL I SHT

Customers Also Bought

TE Part #8-6609940-7  
PM0S0DS6B=C3401

TE Part #CAT-R21-731072  
Bulbous Heat Shrink Boots: Lipped, Straight

TE Part #5-5179010-1  
0.8FH,R13H.5,040,08/Sn,TU

TE Part #1-2301994-2  
RJ45 JACK INT.MAG. 1GB LED 1X1

TE Part #5177984-1  
0.8FH,P05H.5,040,08/Sn,TU

TE Part #3-794634-4  
04P MICRO MNL ASSY,VRT,SMT LF

TE Part #2385692-1  
USB4 RECPTACLE ON BOARD

TE Part #244856-E  
SMCQ 50 M AB VV 8-03 CL \* H007 137 E005

TE Part #5-2176367-0  
RQ 0603 15K 0.1% 10PPM 1K RL

Documents



Product Drawings

TERMINAL,SOLIS SPD 16-14 6

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_2-322996-1\_H.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-322996-1\_H.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_2-322996-1\_H.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

UL Report

English