

# A 1,5 -18 - Ferrule



3202601

<https://www.phoenixcontact.com/us/products/3202601>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Ferrule, Length contact range: 18 mm, sleeve length: 18 mm, color: silver



## Your advantages

- The insulation reliability of close connections is increased and the splicing of wires is prevented
- The dimensions of the ferrules conform to DIN 46228-1
- The ferrules without plastic sleeve are made from soft tin-plated electrolytic copper

## Commercial data

Item number	3202601
Packing unit	1,000 pc
Minimum order quantity	1,000 pc
Sales key	BH34
Product key	BH3412
Catalog page	Page 480 (C-3-2019)
GTIN	4017918165758
Weight per piece (including packing)	0.144 g
Weight per piece (excluding packing)	0.144 g
Customs tariff number	85369010
Country of origin	DE

# A 1,5 -18 - Ferrule



3202601

<https://www.phoenixcontact.com/us/products/3202601>

## Technical data

### Product properties

Product type	Cable end sleeve
Conductor category	stranded conductors, class 2, 5, 6 / B, C, K, M
Product property	UL certified
	Made from soft tin-plated electrolytic copper

### Connection data

#### Conductor connection

Conductor cross section flexible max.	1.5 mm <sup>2</sup>
Conductor cross section AWG max.	16
Stripping length	18 mm

### Dimensions

Dimensional drawing	
Sleeve length	18 mm
Length contact range	18 mm
Maximum stripping length	18 mm
Ferrule diameter	1.7 mm
Sleeve wall thickness	0.15 mm
Inner dimensions of the insulating collar	2.8 mm

### Material specifications

Color	silver-colored
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Surface characteristics	Tin-plated
Components	free from silicone and halogen

### Mechanical properties

Technical data	
Sleeve length	18 mm

### Environmental and real-life conditions

Ambient conditions	
Permanent temperature	105 °C

# A 1,5 -18 - Ferrule

3202601

<https://www.phoenixcontact.com/us/products/3202601>



Short-term temperature

120 °C

## Standards and regulations

Design according to standard

DIN 46228-1, UL 486F-A

# A 1,5 -18 - Ferrule




3202601

<https://www.phoenixcontact.com/us/products/3202601>

## Drawings

Dimensional drawing



Sleeve length (b), insulating collar inner dimension (d), sleeve diameter (k), sleeve wall thickness (j)

# A 1,5 -18 - Ferrule

3202601

<https://www.phoenixcontact.com/us/products/3202601>



## Approvals

ⓘ To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3202601>



**cULus Listed**

Approval ID: E488001

# A 1,5 -18 - Ferrule

3202601

<https://www.phoenixcontact.com/us/products/3202601>



## Classifications

### ECLASS

ECLASS-11.0	27400201
ECLASS-13.0	27400201
ECLASS-12.0	27400201

### ETIM

ETIM 9.0	EC000005
----------	----------

### UNSPSC

UNSPSC 21.0	27121700
-------------	----------

# A 1,5 -18 - Ferrule

3202601

<https://www.phoenixcontact.com/us/products/3202601>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)