




Connectors > Pluggable IO Connectors & Cages



Form Factor: **QSFP28/56**
Pluggable I/O Product Type: **Cage Assembly**
Sealable: **No**
Circuit Application: **Signal**
Operating Temperature Range: **-40 – 85 °C [-40 – 185 °F]**

Features

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Termination Features

Termination Method to PCB	Through Hole - Press-Fit
Termination Post & Tail Length	2.05 mm[.081 in]

Contact Features

PCB Contact Termination Area Plating Material	Tin
---	-----

Dimensions

PCB Thickness (Recommended)	1.57 mm[.062 in]
-----------------------------	------------------

Housing Features

Cage Material	Nickel Silver
---------------	---------------

Body Features

Heat Sink Style	Pin
Heat Sink Finish	Anodized Black
	.165 in



Heat Sink Height Class	PCI
Packaging Features	
Packaging Method	Box & Tray
Configuration Features	
Number of Rear EONs per Port Column	1
Number of Ports	2
Port Matrix Configuration	1 x 2
Operation/Application	
Pluggable I/O Applications	SFP+ Stacked Belly-to-Belly
Circuit Application	Signal
Product Type Features	
Cage Type	Ganged
Thermal Accessory Type Included	Heat Sink
Form Factor	QSFP28/56
Pluggable I/O Product Type	Cage Assembly
Sealable	No
Electrical Characteristics	
Data Rate (Max)	28 Gb/s
Usage Conditions	
Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
Other	
Included Lightpipe	No
EMI Containment Feature Type	Elastomeric Gasket
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2024 (241)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C11-Q17
QSFP56 to QSFP56 Cable Assembly:
26 AWG



TE Part # 1888810-2
EMI/Dust Cover,XFP And QSFP



TE Part # CAT-Q17-N49033
QSFP56-Two QSFP56 Cable
Assembly: 30 AWG



TE Part # CAT-C11-Z8
QSFP28 to QSFP28 Cable Assembly:
26 AWG



TE Part # 1551920-2
zQSFP+ connector assembly



TE Part # CAT-Q17-N490325
QSFP56 to QSFP56 Cable Assembly:
30 AWG



TE Part # 1-2215048-4
ASSY, SEATING TL, QSFP28, 1X2



TE Part # CAT-Q17-N49011
QSFP56-Four SFP56 Cable Assembly:
30 AWG



TE Part # CAT-C11-Z806726

QSFP28 to QSFP28 Cable Assembly:
30 AWG



TE Part # CAT-C11-N49

QSFP28-Two QSFP28 Cable
Assembly: 30 AWG



TE Part # CAT-C11-N490333

QSFP28-Four SFP+ Cable Assembly:
30 AWG



TE Part # CAT-Q17-N490333


QSFP56-Four SFP56 Cable Assembly:
26 AWG



TE Part # CAT-C11-N490325

QSFP28-Four SFP+ Cable Assembly:
26 AWG


Also in the Series | **zQSFP+/QSFP28**



Heat Sinks(7)



Pluggable I/O Cable Assemblies(78)



Pluggable IO Connectors & Cages(424)

Customers Also Bought




TE Part #2007394-5

SFP+assy 2x4 Spring Fingers 4



TE Part #2-5177986-1

0.8FH,P07H.5,040,08/Sn,TR,SC



TE Part #2304452-1

RECEPTACLE COVER WITH GASKET,
CFP2 1X1



TE Part #2057409-1

IMP100S,R,RA2P16C,LG,39




TE Part #2-6450540-5

MBXL VERT RCPT 2P+24S+2P



TE Part #2057417-1

IMP100S,R,RA4P8C,UG,39



TE Part #1871058-3

PCI EXPRESS CONN. EON TYPE, 98



TE Part #394811-E

M12 FEMALE, X CODE, 8P, 17MM
SMT, CAT6A



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2170812-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2170812-1_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2170812-1_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

QSFP28/56 and zQSFP+ Interconnects

English

Product Specifications

Application Specification

English