


GRACE INERTIA 2.0

TE Internal #: 1971032-5
PCB Mount Header, Vertical, Wire-to-Board, 5 Position, 2 mm [.079 in] Centerline, Fully Shrouded, Tin, Through Hole - Solder, GRACE INERTIA 2.0

[View on TE.com >](#)



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**
PCB Mount Orientation: **Vertical**
Connector System: **Wire-to-Board**
Number of Positions: **5**
Number of Rows: **1**

Features

Electrical Characteristics

Operating Voltage	50 VAC
-------------------	--------

Dimensions

Connector Width	5.6 mm[.22 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Height	6.5 mm[.255 in]
Connector Length	12 mm[.472 in]

Packaging Features

Packaging Quantity	300
Packaging Method	Package

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-0

Mechanical Attachment

--	--



Mating Retention	With
Mating Alignment Type	Keyed
PCB Mount Alignment Type	Locating Posts
PCB Mount Retention	Without
PCB Mount Alignment	With
Connector Mounting Type	Board Mount
Mating Alignment	With

Termination Features

Termination Post & Tail Length	2.6 mm[.102 in]
Square Termination Post & Tail Dimension	.5 mm[.02 in]
Termination Method to PCB	Through Hole - Solder

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1 µm[39.37 µin]
PCB Contact Termination Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	2 µm[78.74 µin]
Mating Square Post Dimension	.5 mm[.02 in]
PCB Contact Termination Area Plating Material Thickness	2 µm[78.73 µin]
Contact Layout	Inline
Contact Base Material	Brass
PCB Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Finish	Bright
Contact Mating Area Plating Material	Tin
Contact Type	Tab
Contact Current Rating (Max)	2.2 A

Housing Features

Housing Material	Nylon 66 GF
Centerline (Pitch)	2 mm[.079 in]

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No



Connector & Contact Terminates To	Printed Circuit Board
-----------------------------------	-----------------------

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	5
Number of Rows	1

Body Features

Primary Product Color	Natural
-----------------------	---------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 260°C















Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits



as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 2-1971032-4 4POS HEADER ASSEMBLY FOR GIC 2.0 EV	 TE Part # 1-1971032-2 2POS HEADER ASSEMBLY FOR GIC 2.0 EV	 TE Part # 2-1971032-5 5POS HEADER ASSEMBLY FOR GIC 2.0 EV	 TE Part # 3-1971032-5 5POS HEADER ASSEMBLY FOR GIC 2.0 EV
 TE Part # 2-1971032-6 6POS HEADER ASSEMBLY FOR GIC 2.0 EV	 TE Part # 1-1971032-4 4POS HEADER ASSEMBLY FOR GIC 2.0 EV	 TE Part # 1-1971032-5 5POS HEADER ASSEMBLY FOR GIC 2.0 EV	 TE Part # 2-1971032-2 2POS HEADER ASSEMBLY FOR GIC 2.0 EV
 TE Part # 1971200-1 GIC 2.0 EV 5/8P HEADER ASSEMBLY	 TE Part # 1971032-8 8POS HEADER ASSEMBLY FOR GIC 2.0 EV	 TE Part # 3-1971032-2 2POS HEADER ASSEMBLY FOR GIC 2.0 EV	 TE Part # 2-1971032-3 3POS HEADER ASSEMBLY FOR GIC 2.0 EV
 TE Part # 3-1971032-3 3POS HEADER ASSEMBLY FOR GIC 2.0 EV	 TE Part # 1971032-6 6POS HEADER ASSEMBLY FOR GIC 2.0 EV		

Also in the Series | GRACE INERTIA 2.0




Connector Contacts(4)



PCB Headers & Receptacles(70)




Rectangular Connector Housings(20)



Standard Rectangular Connectors(18)



Wire-to-Board Connector Assemblies & Housings(1)



Wire-to-Board Headers & Receptacles (70)

Customers Also Bought




TE Part #CAT-D9934-A15F
Header Assembly: Wire-to-Board, 5A, gold or tin plated




TE Part #292207-7
MINI CT SGL DIP V 7P NAT




TE Part #CAT-D9934-A15H
DYNAMIC 1900D HDR ASSY



TE Part #173858-1
070 MULTILOCK CAP ASSY 12P



TE Part #179098-1
MULTI LOCK I/O CAP ASSY 30P



TE Part #1-1971032-3
3POS HEADER ASSEMBLY FOR GIC 2.0 EV

Documents

Product Drawings

5P HEADER ASSEMBLY FOR GIC 2.0 EV

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1971032-5_D.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1971032-5_D.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1971032-5_D.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English