




Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Receptacle**

PCB Mount Orientation: **Vertical**

Connector System: **Board-to-Board**

Number of Positions: **128**

Number of Rows: **4**

Features

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
Stack Height	15.24 mm[.6 in]
Connector Width	14.85 mm[.585 in]
PCB Thickness (Recommended)	2.36 mm[.093 in]
Connector Height	10.16 mm[.4 in]

Packaging Features

Packaging Quantity	5
Packaging Method	Tube

Usage Conditions

Housing Temperature Rating	High
Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]

Operation/Application

Assembly Process Feature	None
Circuit Application	Signal

Mechanical Attachment

Mating Alignment Type	Polarized
PCB Mount Retention Type	Mounting Hole



PCB Mount Retention	With
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Termination Features

Rectangular Termination Post & Tail Width	.51 mm[.02 in]
Rectangular Termination Post & Tail Thickness	.25 mm[.01 in]
Termination Post & Tail Length	3.78 mm[.149 in]
Termination Method to PCB	Through Hole - Solder

Contact Features

Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Mating Square Post Dimension	.64 mm[.025 in]
Contact Shape & Form	Four Beam
Contact Layout	Matrix
Contact Base Material	Beryllium Copper
PCB Contact Termination Area Plating Material	Tin-Lead
Contact Mating Area Plating Material	Gold
Contact Type	Socket
Contact Current Rating (Max)	3 A

Housing Features

Housing Material	Polyphenylene Sulfide (PPS)
Centerline (Pitch)	2.54 mm[.1 in]

Configuration Features

Number of Columns	32
Number of Loaded Positions	128
Board-to-Board Configuration	Perpendicular
Stackable	No
PCB Mount Orientation	Vertical
Number of Positions	128
Number of Rows	4

Product Type Features

PCB Connector Assembly Type	PCB Mount Receptacle
-----------------------------	----------------------



Connector System	Board-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Body Features

Primary Product Color	Brown
-----------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.




Customers Also Bought




TE Part #5222092-1
JACK,RTANG,PCB,75 OHM,BNC




TE Part #1888247-2
20 POS SMT CONN, SFP/SFP+, 15A




TE Part #499252-7
060 STRAIN RELIEF A-L RCPT




TE Part #321035
PIDG 26-22 SPADE #4 STUD




TE Part #5-102618-4
12 MODII HDR DRST SHRD .100CL




TE Part #52454
PG SPR SPD 22-16COMM 22-18MIL8




TE Part #2-2176308-2
RP 1E 0.1W 221K 0.1% 25PPM 5K RL



TE Part #2-1617030-1
HFW1201F01M = M39016/6-123M



TE Part #1617122-2
JMACD-12XM = M39016/15-079M



TE Part #5-1617785-1
FCA-410-1517L=M83536/15-017L

Documents

Product Drawings
BOX II 4 ROW RECP ASSY 128 POS

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_5-533285-3_W.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_5-533285-3_W.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_5-533285-3_W.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

5-533285-3

PCB Mount Receptacle, Vertical, Board-to-Board, 128 Position, 2.54 mm [.1 in]
Centerline, Gold, Through Hole - Solder, Signal, Brown, Tube



Product Specifications

Product Specification

English