




Connectors > Connector Accessories > Heat Sinks



Device Type: CFP2

Fin Style: Unidirectional

Number of Fins: 11

EU RoHS Compliance: Compliant

EU ELV Compliance: Compliant

Features

Body Features

Primary Product Material	Aluminum
Primary Product Plating Material	Black Anodized
Fin Style	Unidirectional

Product Type Features

Device Type	CFP2
-------------	------

Configuration Features

Number of Fins	11
----------------	----

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts




TE Part # 2288221-1
CFP2 EMI/DUST PLUG




TE Part # 2288220-2
CFP2 HEATSINK CLIP


Customers Also Bought




TE Part #170151-2
FF 250 TAB 18-14AWG PTBR



TE Part #282834-6
TERMI-BLOK PCB MOUNT, 90 6P.



TE Part #1546551-2
2P, STRAIGHT, SIDE ENTRY, 3.5MM



TE Part #2274845-1
CFP2 RECEPTACLE ASSEMBLY



TE Part #2305018-2
USB TYPE C, REC IPX8 ON BOARD
DUAL SMT




TE Part #ADP-SMAF-NF-B-W
SMA Jack to N Jack



TE Part #ANT-5GW-IPW3-NP
Antenna 5GW LPWA ISM IP67 N-Plug



TE Part #3-1676914-7
YR1 0.1% 47K5



BATTERY CON

Documents

Product Drawings
HEAT SINK,FRONT TO BACK AIREFLOW,CFP2
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2288218-6_1.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_2288218-6_1.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_2288218-6_1.3d_stp.zip
English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications
Application Specification
English