




EMI & EMC Solutions > EMI Filters > Power Line Filters > Single Phase Filters > Single Phase Filters, Corcom K Series



Current Rating: 10 A

Input Termination Type: IEC

Output Termination Type: .250" FASTON

Leakage Current (Max) (120VAC, 60Hz): .21 mA

Leakage Current (Max) (250VAC, 50Hz): .36 mA

[All Single Phase Filters, Corcom K Series \(34\)](#)

Features

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Product Type Features

Filtering Requirements	Filtered
Ground Choke Option	No
Input Termination Type	IEC
Output Termination Type	.250" FASTON

Electrical Characteristics

Current Rating	10 A
Leakage Current (Max) (120VAC, 60Hz)	.21 mA
Leakage Current (Max) (250VAC, 50Hz)	.36 mA
Operating Voltage	250 VAC



Other

EU RoHS Compliance	Compliant with Exemptions
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.1% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-C8114-K1
Single Phase Filters, Corcom K Series

Also in the Series

Corcom K

Single Phase Filters(34)

Customers Also Bought

TE Part #1609133-3
6ESRM-3=F6920

TE Part #5205817-3
FEMALE SCREWLOCK KIT

TE Part #5207719-3
KIT SCREWLOCK FEMALE CLEAR ZIN

TE Part #5-87631-1
60 MODIV HSG COMP DR .100 POL

TE Part #YDTS26W11-98PAV001
PLUG ASSY

TE Part #1757820-6
AMPLIMITE,ASY,RCPT,STD,109,ZN,1, CT

TE Part #1757819-6
AMPLIMITE,ASY,PLUG,STD,109,ZN,1, CT

TE Part #CQ50453001
RAY-101-6.0(10)

TE Part #5748677-1
PLTD PLST CBL CLMP KIT,SZ 1

TE Part #855366-000
382A012-25/225-0



Documents

Product Drawings

10EK7M=F7096 S0

English

CAD Files

Customer View Model

ENG_CVM_CVM_1-6609027-6_B1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-6609027-6_B1.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_1-6609027-6_B1.2d_dxf.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654001_CORCOM_PRODUCT_GUIDE_K_SERIES

English

Corcom Combined Selector Charts

English

1-1654250-1_CORCOM_EMI_RFI_QRG

English