



Terminals & Splices > PCB Terminals



PCB Terminal Type: **Tab**
PCB Thickness (Recommended): **3.18 mm [.125 in]**
Mating Tab Width: **6.35 mm [.25 in]**
Mating Tab Thickness: **.81 mm [.032 in]**
PCB Hole Diameter: **1.4 mm [.055 in]**

Features

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-30 – 110 °C[-22 – 230 °F]

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Dimensions

Extension Below Board	3.18 mm[.125 in]
Terminal Material Thickness	.81 mm[.032 in]
PCB Thickness (Recommended)	3.18 mm[.125 in]
PCB Hole Diameter	1.4 mm[.055 in]
Profile Height from PCB	12.62 mm[.503 in]

Contact Features

PCB Contact Termination Area Plating Material Thickness	3.81 µm[150 µin]
Contact Underplating Material Thickness	2.54 µm[100 µin]



Contact Mating Area Plating Material Thickness	3.81 μm[150 μin]
PCB Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Plating Material	Tin
Terminal Size	6.35
Terminal Orientation	Straight

Termination Features

Termination Method to PCB	Through Hole - Solder
Product Terminates To	Printed Circuit Board

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 265°C





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 63849-1 250 FASTON TAB TPBR	 TE Part # 1217056-1 250 FASTON,PCB TAB,TPBR	 TE Part # 1217756-1 187 FASTON,TAB,TNBR	 TE Part # 1217421-1 250 FASTON,PCB TAB,TNBR
 TE Part # 1217167-1 250 FASTON,PCB TAB,TCBR	 TE Part # 1742188-1 250 FASTON,PCB TAB,TCBR	 TE Part # 735427-2 110 FASTON TAB TPBR	 TE Part # 1217169-1 250 FASTON,PCB TAB,TCBR
 TE Part # 62262-1 250 FASTON TAB TPBR	 TE Part # 62409-1 250 FASTON TAB TPBR	 TE Part # 63849-4 250 FASTON TAB SPBR	 TE Part # 1217754-1 250 FASTON,FLAG,PCB TAB,TNBR
 TE Part # 1-1217056-0 250 FASTON,PCB TAB,TPBR	 TE Part # 63067-1 250 FASTON TAB TPBR	 TE Part # 1217057-1 187 FASTON,PCB TAB,TPBR	 TE Part # 62437-1 110 FASTON TAB TPBR



TE Part # 61134-3
110 FASTON TAB TPBR

TE Part # 1742686-1
250 FASTON,PCB TAB,TCBR

TE Part # 1742803-1
FASTON 312 PCB TAB TPBR

Also in the Series | FASTON 250

Compression Connectors(4)

Crimp Terminal Housings(132)

Insertion & Extraction Tools(6)

Magnet Wire Terminals(1)

PCB Terminals(134)

Quick Disconnects(425)

Splices(4)

Customers Also Bought

TE Part #66580-2
TYPE VI SKT CONT,MULTI-MATE

TE Part #2176081-3
EP 1W (S) 22R 5%

TE Part #6-1415899-6
RZHH-1A4-D012

TE Part #5052844025
RNF-100-3/64-0-SP

TE Part #926933-1
WIRE PIN 18-17 AWG .01 PTPB

TE Part #2-1735042-9
1MM FFC SMT V ASSY 29P EMBOSS

TE Part #4-1744524-3
3.96 EP HDR ASY 03P ,NO 2 PIN, GW

TE Part #7-147729-0
21 MODIV VRT SR SFMNT SN



TE Part #7-1393788-8
[V23079G1005B301](#)



TE Part #1217956-1
[312 FASTON,PCB TAB,TCBR](#)

Documents

Product Drawings

[250 FASTON TAB TPBR](#)

English

CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_63900-1_G_c-63900-1-g.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63900-1_G_c-63900-1-g.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63900-1_G_c-63900-1-g.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[FASTON PCB Tabs and Receptacles](#)

English

[PRINTED CIRCUIT BOARD TERMINALS AND DISCONNECTS](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[CSA Certificate](#)

English

[CSA Certificate](#)

English