




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Tab**

Wire Size: **4 – 6.63 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Mechanical Attachment

Locking Lance Height	1.4 mm
Wire Insulation Support	With
Mating Retention Type	Locking Lance

Packaging Features

Packaging Quantity	500
Packaging Method	Loose Piece/Carton

Dimensions



Product Length	29 mm[1.14 in]
Compatible Insulation Diameter Range	3.43 – 5.08 mm[.135 – .2 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	4 – 6.63 mm²

Product Type Features

Insertion Force	Normal
-----------------	--------

Contact Features

Quick Disconnect Terminal Type	Tab
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Open

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 180250
HHHT FSTON/FF 375 POS LOC 250 6-2 ASSY

TE Part # 1-1579007-4
EXTRACTION TOOL

TE Part # 4-1579007-3
EXTRACTION TOOL KIT

TE Part # 928906-2
FF 110 TAB 20-15 AWG .016 TPPB

TE Part # 2379381-2
SDE F, FASTIN-FASTON, 4.0-6.0mm2, DIE SET

TE Part # 641256-1
BLADE TAB 250 18-14AWG BR LP

TE Part # 2379381-1
SDE F, FASTIN-FASTON, 4.0-6.0mm2, ASSY

TE Part # 154660-2
FASTON 250 TAB 22-18 AWG TPBR

Also in the Series | FASTIN-FASTON 250

Crimp Terminal Housings(207)

Insertion & Extraction Tools(2)

PCB Terminals(2)

Quick Disconnects(250)

Customers Also Bought



TE Part #1625984-5
HSA50 10R 5%



TE Part #T4112511041-000
M12 F, 4P GOLD D_CODE RA SHIELDED PG7



TE Part #350811-1
STR/REL CLAMP



TE Part #T4113401051-000
M12,MALE,RA,B CODE,5P,PG7,GOLD



TE Part #K1121830
Relay 29-011-02A



TE Part #K1131360
Battery Disconnecter 35-514-231-R-900



TE Part #1-480701-5
03P UMNL CAP HSG GRN



TE Part #K1008784
Relay 26-56-02



TE Part #D01671-000
HEL-6880.3-ARG



TE Part #1-1102314-6
HB.24.STS.1.21

Documents

Product Drawings

FF 250 TAB 4-6MM2 PTBR LP

English

FF 250 TAB 4-6MM2 PTBR LP

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_180409-2_F_c-180409-2-f.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_180409-2_F_c-180409-2-f.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_180409-2_F_c-180409-2-f.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Specifications

FASTIN-FASTON CONN. .110 INCH, .187 INCH, .250 INCH, .375 INCH SRS.

English

Product Specification

English