




MQS

TE Internal #: 2-967642-2

TE Internal Description: MQS BU-GEH,EDS 3P

MQS, CONNECTOR HOUSING

[View on TE.com >](#)



All MQS, CONNECTOR HOUSING (353)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Octamethylcyclotetrasiloxane (D4) (.5% in Component Part) Dodecamethylcyclohexasiloxane (D6) (.5% in Component Part) Decamethylcyclopentasiloxane (D5) (.5% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 968401-1 MQS2.KONT-SICHERUNG	 TE Part # 936459-2 MQS 3P COVER HSG	 TE Part # 2-968403-2 MQS BU-GEH 3P,GRAU	 TE Part # 1-967167-6 3POS MQS TAB SEALED COD A
 TE Part # 968402-2 MQS SCHUTZKAPPE, 3P	 TE Part # CAT-M8793-T273 MQS, RECEPTACLE AND TAB		

Customers Also Bought

 TE Part #170454-2 PL 250 AM REC 18-14 0.40 X 21 PRE-TPBR	 TE Part #2298633-1 60POS,HYBRID,REC HSG ASSY, UNSLD,COD A	 TE Part #2355073-1 6POS,AMP MCP 2.8,REC HSG,UNSLD, COD A,GRY	 TE Part #2366066-1 48POS,MCON 1.2,TAB HSG ASSY, UNSLD,COD A
 TE Part #2377789-4 TAB1.2X0.6,TERMINAL,SWS,REM 1.2,1.0MM2	 TE Part #936092-1 090III 10P PLUG ASSY	 TE Part #2278398-1 3WAY GET 0.64 SEAL PLUG	 TE Part #2-2355506-1 2POS,MCON 1.2,REC HSG ASSY,SLD, COD B
 TE Part #2367937-2 FAW D357 VW AKII 90D PIGTAIL	 TE Part #2379006-3 52POS,HYBRID,REC HSG ASSY		



Documents

Product Drawings

MQS BU-GEH,EDS 3P

English

CAD Files

Customer View Model

ENG_CVM_CVM_2-967642-2_B.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-967642-2_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-967642-2_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English