


EMI & EMC Solutions > EMI Filters > Power Line Filters > Single Phase Filters > Single Phase Filters, Corcom WG Series



Current Rating: **16 A**

Input Termination Type: **.250" FASTON**

Output Termination Type: **.250" FASTON**

Leakage Current (Max) (120VAC, 60Hz): **.1 mA**

Leakage Current (Max) (250VAC, 50Hz): **.2 mA**

[All Single Phase Filters, Corcom WG Series \(9\)](#)

Features

Usage Conditions

Operating Temperature Range	-10 – 40 °C
-----------------------------	-------------

Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Product Type Features

Filtering Requirements	Filtered
Ground Choke Option	No
Input Termination Type	.250" FASTON
Output Termination Type	.250" FASTON

Electrical Characteristics

Current Rating	16 A
Leakage Current (Max) (120VAC, 60Hz)	.1 mA
Leakage Current (Max) (250VAC, 50Hz)	.2 mA
Operating Voltage	250 VAC

Other

EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant

Product Compliance

For compliance documentation, visit the product page on [TE.com](https://te.com)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | Corcom WG



Single Phase Filters(9)

Customers Also Bought

TE Part #6609021-4
2VB3=F7123 S0TE Part #8-1393211-4
T92S11A22-120TE Part #1-1879453-9
TE 1000W 33R 5% BracketTE Part #TAB62435501-002
M12B2-FR-PUR-1.0MTE Part #3-1393250-3
W28-XQ1A-20=W28TE Part #5-1437652-4
6PCV-03-006=6PCV ASSEMBLYTE Part #3-1609037-8
20EH1=F8366TE Part #284506-9
9 POS TERMI-BLOK PLUG STACK 3,TE Part #2840900-1
2POS,HC-STAK 25,REC OUTER HSG
ASSY,PLUGTE Part #0068670003
TRSA-1019/G/1/1

Documents

Product Drawings

[16WGF1=F4338E](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_4-6609089-8_E1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-6609089-8_E1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_4-6609089-8_E1.2d_dxf.zip](#)

English

[3D PDF](#)

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654001_CORCOM_PRODUCT_GUIDE_WG_SERIES](#)

English

[Corcom Combined Selector Charts](#)

English

[1-1654250-1_CORCOM_EMI_RFI_QRG](#)

English